



Part Number : [1202530181](#)
Product Description : Contrinex Inductive Sensor, M30 Housing, 0 - 20mm Operating Distance, Quasi-embeddable, Analog, 0 - 10V Output, 4-pin M12 Connector, 48.5mm Housing Length
Series Number : 120253
Status : Not Recommended For New Design
Product Category : Inductive and Photoelectric Sensors
Engineering Number : DW-AS-509-M30-320




Documents & Resources

Specifications

[1202530178-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Not Recommended For New Design
Category	Inductive Sensors
Series	120253
Description	Contrinex Inductive Sensor, M30 Housing, 0 - 20mm Operating Distance, Quasi-embeddable, Analog, 0 - 10V Output, 4-pin M12 Connector, 48.5mm Housing Length
IP Rating	IP67
Product Name	Contrinex
Type	Inductive
UPC	191130063512

Electrical

Output	0-10V
Polarity	Analog

Physical

Connection	Connector (M12, 4-pin)
Length	48.5mm
Material - Housing	Chrome Plated Brass
Material - Sensing Face	PBTP
Mounting Style	Quasi-embeddable
Net Weight	152.000/g

Operating Distance	0 - 20mm
Output	0-10V
Sensor Housing Size	M30
Temperature Range - Operating	-25° to +70°C

This document was generated on Sep 22, 2025