



**Part Number :** [1200270752](#)  
**Product Description :** Nano-Change (M8)  
Single-Ended Cordset, 5 Poles, B-Coded, Male  
(Straight) to Pigtail, 0.25mm<sup>2</sup> PUR/PVC Cable,  
2.0m (6.56') Length, PUR Cable Preferred  
Version in Europe  
**Series Number :** 120027  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** 405006P02M020



Documents & Resources

Drawings  
[1200270752\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120027
Description	Nano-Change (M8) Single-Ended Cordset, 5 Poles, B-Coded, Male (Straight) to Pigtail, 0.25mm <sup>2</sup> PUR/PVC Cable, 2.0m (6.56') Length, PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Nano-Change (M8)
Protocol	N/A
Type	Single Ended
UPC	883906204600

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V

### Physical

Cable Diameter	5.08mm (.200")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy

Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	78.100/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A

---

This document was generated on Apr 20, 2025