



**Part Number :** [1212070106](#)  
**Product Description :** mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 230V, Amber LED, Transparent, Nitrile Gasket  
**Series Number :** 121207  
**Status :** Active  
**Product Category :** Circular Industrial Connectors  
**Engineering Number :** S28200TC4M0R



Documents & Resources

**Drawings**  
[Drawing 1212070106\\_sd.pdf](#)

**Specifications**  
[Packaging Specification PK-121207-S28-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

- Multiple Part Product Compliance Statements
- Eu RoHS
  - REACH SVHC
  - Low-Halogen

- Multiple Part Industry Compliance Documents
- IPC 1752A Class C
  - IPC 1752A Class D
  - Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Connectors
Series	121207
Description	mPm DIN Valve Connector, Form A-18mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 230V, Amber LED, Transparent, Nitrile Gasket
IP Rating	IP65, IP67
Product Family	mPm DIN Valve Connectors
Product Name	mPm
Type	Field Attachable Connector
UPC	884982414112

#### Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	230V

#### Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	Yes
Diagnostics Port	No
Form	A - 18mm
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver

Orientation	90° Angle
Pitch - Mating Interface	18.00mm
Poles	2
Temperature Range - Operating	-40°C to +90°C
Wire Size (AWG)	N/A

---

This document was generated on Dec 11, 2023