

Part Number : 1202540136
Product Description : Contrinex Photoelectric Sensor, M18 Housing, Diffuse, NPN, Changeover, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable, 50mm Housing Length
Series Number : 120254
Status : Obsolete
Product Category : Inductive and Photoelectric Sensors
Engineering Part Number : LTK-1180-101

Documents and Resources

Specifications

1202540136-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Obsolete

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Obsolete
Category	Photoelectric Sensors
Series	120254
Description	Contrinex Photoelectric Sensor, M18 Housing, Diffuse, NPN, Changeover, Potentiometer Sensitivity Adjustment, 2m 4-wire PVC Cable, 50mm Housing Length
IP Rating	IP67
Operating Principle	Diffuse
Product Name	Contrinex
Type	Photoelectric
UPC	191130068920

Electrical

Output	Changeover
Polarity	NPN
Switching Frequency	≤ 1000 Hz

Physical

Connection	Cable (PVC 2m, 4-wire)
Length	50mm
Material - Housing	Chrome Plated Brass
Material - Window	Glass
Output	Changeover
Sensor Housing Size	M18
Temperature Range - Operating	-25° to +55°C

Obsolete

Downloaded from Arrow.com.