



Product: [9418](#) 

Electronic, 4 C #18 Str TC,SRPVC Ins, OS, PVC Jkt, CMG

 [Request Sample](#)

Product Description

Electronic, 4 Conductor 18AWG (19x30) Tinned Copper, SRPVC Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

Element	AWG	Stranding	Material	No. of Conductors
Conductor(s)	18	19x30	TC - Tinned Copper	4

Conductor Count:	4
------------------	---

Insulation

Element	Material	Nominal Wall Thickness
Conductor(s)	S-R PVC - Semi-Rigid Polyvinyl Chloride	0.011 in

Color Chart

Number	Color
1	Red
2	Green
3	Black
4	White

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Alum / Poly	Beldfoil® (Z-Fold®)	100 %	TC - Tinned Copper	20	Stranded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.245 in	0.035 in

Construction and Dimensions

Cabling

Lay Direction	Twists
Left Hand	6 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
6.5 Ohm/1000ft	8.5 Ohm/1000ft

Capacitance

--	--

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
40 pF/ft	72 pF/ft

Current

Element	Max. Recommended Current [A]
10C Temperature rise	5.0 Amps per conductor @ 25°C ambient

Voltage

UL Description	UL Voltage Rating
CMG	300 V
UL AWM 2464	300 V

Temperature Range

UL Temp Rating:	80°C (UL AWM 2464)
Operating Temp Range:	-20°C to +80°C

Mechanical Characteristics

Bulk Cable Weight:	42 lbs/1000ft
Max Recommended Pulling Tension:	100 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	2464
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	89418 or 82418

Part Number

Variants

Item #	Color	UPC
9418 060100	Chrome	612825240631
9418 0601000	Chrome	612825240648
9418 06010000	Chrome	612825240655

9418 06013000	Chrome	612825240679
9418 060500	Chrome	612825240686
9418 0605000	Chrome	612825240693
9418 060U1000	Chrome	612825240617
9418 060U500	Chrome	612825240624

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Y - FINAL PUT-UP LENGTH MAY VAR -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.
Footnote:	Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

History

Update and Revision:	Revision Number: 0.320 Revision Date: 05-27-2020
----------------------	--

© 2020 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.