







REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	MAY.18/16	L.CHAN



- NOTES:
- MATERIALS**
HOUSING: ENGINEERING THERMOPLASTIC.
CONTACTS: COLOUR: BLACK. FLAMMABILITY RATING UL 94V-0
PLATING: PHOSPHOR BRONZE
6 m" [0.1524 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 m" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 m" [2.54 MICRONS]
MIN. MATTE-TIN ON CONTACT TAILS.
SHIELD: COPPER ALLOY
NICKEL PLATED WITH TIN DIPPED TAIL.
 - RECOMMENDED SOLDERING TEMPERATURE:**
WAVE SOLDERING TEMPERATURE AT 260°C MAXIMUM FOR 10 SEC MAXIMUM
 - AMPHENOL PART NUMBER:** RJSNE-GF8X-08



UNLESS SPECIFIED OTHERWISE		DRAWN Jack Guo	MAY18.16	Amphenol Canada Corp. www.amphenolcanada.com	
PRIMARY UNITS: INCHES		CHECKED			
SECONDARY: MILLIMETERS		M.E. APP'D			
		Q.A. APP'D			
1 DECIMAL PLACE		DWG APP'D L.CHAN	MAY18.16	STACKABLE MODULAR JACK 2X4 PORTS, 8 POSITIONS, 8 CONTACTS, WITH LEDS, SHIELDED, TRAY PACKAGING -RoHS COMPLIANT	
2 DECIMAL PLACES		ENG. REL. NO.			
3 DECIMAL PLACES		REF.			
ANGULAR DEGREES ±.015		THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	DWG NO. P-RJSNE-GF8X-08	REV A
		CODE ID NO. 03554	DWG SIZE	SCALE	SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.