Product data sheet

Specifications



APC Smart-UPS X, Line Interactive, 2200VA, Rack/tower convertible 2U, 100V-127V, 6x 5-15R+2x 5-20R NEMA, SmartSlot, Extended runtime

SMX2200RMLV2U

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.

Main

Main input voltage	120 V AC
Other input voltage	100 V 110 V 127 V
Input connection	NEMA L5-30P
Efficiency at full load	70...153 V
Input frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V AC 1 phase
Other output voltage	100 V 110 V 127 V
Rated power in W	1980 W
Rated power in VA	2200 VA
Output connection	6 NEMA 5-15R 2 NEMA 5-20R
Harmonic distortion	Less than 5 %
Maximum configurable power in VA	2200 VA
Maximum configurable power in W	1980 W
Transfer time	2-4 ms 4 ms typical : 8 ms maximum
UPS topology	Line interactive
Waveform type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Replacement battery	APCRBC117

Graphs

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph

Complementary

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Downloaded from Arrow.com.

Battery type	Lead-acid internal included
Control panel	Multifunction LCD status and control console
Emergency power off	Yes
Free slot	1
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
UPS connectivity	Serial port USB port Available expansion slot
Surge energy rating	540 J
Noise filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449
Number of rack unit	2U
Cable length	2.4 m
Number of cables	1
Color	Black
Height	85 mm
Width	431.8 mm
Depth	667 mm
Product weight	38.45 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting mode	Rack-mounted with included kit
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack mounting brackets Rack mounting support rails Removable support feet Smart UPS signalling RS-232 cable USB cable
Number of power modules	0
Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Extended run
Redundant	No
Range of product	Smart-UPS
Product or component type	Uninterruptible power supply (UPS)

Environment

Downloaded from Arrow.com.

Product certification	BSMI CSA NOM TÜV VCCI class A
Equipment protection policy	Lifetime : $150000
Ambient air temperature for operation	0…40 °C
Ambient air temperature for storage	-15…45 °C
Storage altitude	0…15240 m
Relative humidity	0…95 %
Storage relative humidity	0…95 %
Acoustic level	55 dBA
Heat dissipation	268 Btu/h
Operating altitude	0...10000 ft

Batteries & Runtime

Battery type	Lead-acid battery
Extendable runtime	1
Included battery module	0
Empty battery slot	0
Typical recharge time	3 h
RBC quantity	1
Battery life	3…5 year(s)
Battery charging power	233 W rated

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24.3 cm
Package 1 Width	86.9 cm
Package 1 Length	59.6 cm
Package 1 Weight	45.36 kg
Pallet unit layers	2
Pallet layers	4

Contractual warranty

Warranty (in months)	24 Battery|36 UPS

Downloaded from Arrow.com.

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**2 867 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**1 498 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**0 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**18 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**1 348 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**4 kg CO2 eq.**
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	**Yes**
Packaging without single use plastic	**No**
EU RoHS Directive	Compliant By Exemption
REACh Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	**WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov**

Energy efficiency

Energy Efficiency Optimized	**Energy efficient product**

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**58**
End of life manual availability	End of Life Information
Removable battery	**User replaceable**
Take-back	**No**

Downloaded from Arrow.com.

WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Downloaded from Arrow.com.

Image of product / Alternate images

Alternative





Downloaded from Arrow.com.





Downloaded from Arrow.com.



Downloaded from Arrow.com.