





APPROVED: _____

DATE: _____ TITLE: _____



Rev	AWO #	Description	Date	Appr
-		RELEASED	3/7/13	
A		UPDATED DRAWING	11/20/17	HR/IC



RECOMMENDED PCB LAYOUT



SECTION A-A



ASSEMBLY VIEW

PACKAGED ON TAPE & REEL

Positions: 02 thru 15

A = .059 [1.50] X No. of Spaces

B = .059 [1.50] X No. of Positions + .118 [3.00]

C = .059 [1.50] X No. of Positions + .024 [0.60]

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 50 AC/DC

Current rating: 1 AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			TITLE		
DATE			.059 [1.50] TOP ENTRY TYPE, SMT TYPE		
DRAWN	AY	3/7/13	SIZE	PART NO.	REV.
CHECKED	CC	3/7/13	X	15SH-A-XX-TS-SMT-PP-T/R	A
APPROVED			REF:	S00124T	SCALE: NTS
					SHEET 1 OF 1