







	1	2	3	4	5	6	7						
A	 Panel Thickness Screw L=5.0 For Panel Thickness Under 1.2mm Screw L=6.0 For Panel Thickness Between 1.2-2.0mm  Recommended Panel Cut-Out		    15 Pin Female Connector PCB Pin Layout Scale 2:1 NOTES: MATERIAL 1.Insulator Material: Black,NYLON+G/F UL94V-0 ② 2.Contact Material: Copper Alloy ② 3.Plating: 1u" Gold Plating 4.Waterproof Rate: IP67 5.Do Mating Test After Glued ② Electrical 1.Contact resistance: 20mΩ max. 2. Insulation resistance: 500MΩ min. at DC500V 3.Dielectric withstanding voltage: 500V AC 1 minute 4.Rating current: 2A 5.Durability: 500 cycles 6.Temperature range: -20°C ~ +85°C 7.Wave soldering temp.: +220°C 10s max.					A					
B								B					
C								C					
D								D					
E								E					
F								F					
G	RoHS compliant Unit:mm		Scale	Free				Date	Name	Description: 15 Pin Female Connector	G		
TOLERANCE							Drawn	24.12.2008	JACK				
X.X			±0.25					Approved	03.08.2020	Segal	ASSMANN WSW-No.		
X.XX			±0.10								A-DF 15 AA-WP		
X.XXX			±0.05	③	Add the screw spec on page 2	03.08.2020	Segal						
H			DIM	TOL	②	Change dimension and add notes	24.01.2018	Segal		Drawing-No.	ASS 3251 CO	rev03	H
					①	Drawn	24.12.2008	JACK					
			Angle	±1°	Id.	Modification	Date	Name	Customer-No.		SHEET 1 / 2		
	1	2	3	4	5	6	7						

