

## USB 3.0 to Gigabit Ethernet NIC Network Adapter - 10/100/1000 Mbps, Black

MODEL NUMBER: U336-000-R



USB 3.0 Gigabit Ethernet adapter connects your laptop to a wired Ethernet network for 10/100/1000 Mbps data transfer speeds.

### Features

**USB 3.0 to Gigabit Ethernet Adapter Connects You to a Wired 10/100/1000 Mbps Network** This USB 3.0 Gigabit Ethernet NIC network adapter instantly connects your computer, laptop, notebook, MacBook, Ultrabook or Chromebook to a 10/100/1000 Mbps network through a USB port. No internal Ethernet card is required. Just connect the built-in USB plug to your computer, and use a Cat5e/6 cable (sold separately) to connect the RJ45 end to a wired Gigabit Ethernet network. This network adapter is ideal for use in areas where Wi-Fi is unavailable or a wired connection offers faster speeds.

**Compliant with State-of-the-Art USB 3.0 Speeds** Because this Gigabit Ethernet adapter complies with USB 3.0 (5 Gbps) specifications, you are ensured true 10/100/1000 Mbps network speed without a compromise in signal quality.

**Plug-and-Play Operation Lets You Begin Transferring Data Almost Immediately** No external power is required. Just connect the adapter to both your computer and an RJ45 Gigabit Ethernet port for network access without the need to find an AC outlet. The lightweight unit is easy to carry in a pocket, purse, backpack or laptop bag for instant file transfers where needed. It's compatible with Windows, Mac and Linux.

**Manufactured to Exacting Standards to Ensure a Full Ethernet Experience** This USB 3.0 Gigabit Ethernet adapter complies with IEEE 802.3 (10Base-T), 802.3u (100Base-TX), 802.3ab and 802.3az (Energy Efficient Ethernet) standards. It supports full- and half-duplex operations, suspend mode and remote wakeup via link-up and magic packet. Diagnostic LEDs indicate when you are connected to a network and when data is being transferred.

### Highlights

- Connects your laptop to a Gigabit Ethernet network when Wi-Fi is unavailable
- Supports true 10/100/1000 Mbps Ethernet network speeds for fast downloads
- USB 3.0 compatibility allows large data transfers with no compromise in signal quality
- Diagnostic LEDs indicate when you are connected to a network and when data is being transferred.
- Plug-and-play operation allows you to set it up and begin using it immediately
- Small enough to carry in a pocket or purse for fast file transfers anywhere

### Applications

- Connect to a wired Gigabit Ethernet network in an office, trade show booth, lecture hall, classroom, hotel lobby or auditorium
- Extend the life of a legacy laptop or notebook computer with a failed internal Ethernet card
- Play network gaming consoles in areas without Wi-Fi capability

### System Requirements

- IBM-compatible Pentium 233 MHz or faster PC or Mac
- 64 MB RAM or more
- USB-A port (USB 3.0 port required to achieve USB 3.0 speeds)
- Windows (XP through 11), Mac (10.6 through 10.12) or Linux Kernel (2.6.25 and later) operating system

### Package Includes

- U336-000-R USB 3.0 to Gigabit Ethernet NIC Network Adapter, Black
- Driver CD
- Quick Start Guide

## Specifications



Powering Business Worldwide

TRIPP LITE  
SERIES

| OVERVIEW                        |                                         |
|---------------------------------|-----------------------------------------|
| UPC Code                        | 037332174925                            |
| Technology                      | Cat5/5e; Cat6                           |
| INPUT                           |                                         |
| Bus Powered                     | Yes                                     |
| Product Length (in.)            | 7.5                                     |
| POWER                           |                                         |
| Power Consumption (Watts)       | 0.50                                    |
| CONNECTIONS                     |                                         |
| Side A - Connector 1            | USB 3.0 A (MALE)                        |
| Side B - Connector 1            | RJ45 (FEMALE)                           |
| Connector Plating               | Nickel                                  |
| PHYSICAL                        |                                         |
| Color                           | Black                                   |
| Material of Construction        | ABS, PVC                                |
| Cable Jacket Rating             | VW-1                                    |
| Shipping Dimensions (hwd / in.) | 0.79 x 4.72 x 3.94                      |
| Shipping Weight (lbs.)          | 0.09                                    |
| Unit Dimensions (hwd / in.)     | 0.000 x 0.000 x 0.000                   |
| Unit Packaging Type             | Box                                     |
| Unit Weight (lbs.)              | 0.06                                    |
| Unit Weight (kg)                | 0.03                                    |
| ENVIRONMENTAL                   |                                         |
| Operating Temperature Range     | 32° to 158°F (0° to 70°C)               |
| Storage Temperature Range       | 14° to 176°F (-10° to 80°C)             |
| Relative Humidity               | 10% to 90 % RH, Non-Condensing          |
| BTUs                            | 1.7 BTU/Hr                              |
| COMMUNICATIONS                  |                                         |
| Network Compatibility           | 1 Gbps (Gigabit)                        |
| IEEE Standards Supported        | 802.3; 802.3ab; 802.3az; 802.3u; 802.3x |
| FEATURES & SPECIFICATIONS       |                                         |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                                      |
|-------------------------------------|------------------------------------------------------|
| USB Specification                   | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |
| Auto MDIX Support                   | Yes                                                  |
| Full Duplex Support                 | Yes                                                  |
| Suspend Mode Support                | Yes                                                  |
| Remote Wakeup Support               | Yes                                                  |
| Driver Required                     | Yes                                                  |
| Recommended Category Cable          | Cat5/Cat5e/Cat6 Cables                               |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                                      |
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA)                  |
| <b>WARRANTY &amp; SUPPORT</b>       |                                                      |
| Product Warranty Period (Worldwide) | 3-year limited warranty                              |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.