





PRODUCT NUMBER

PITCH

0Qxx53x000J0G

5.08 mm


 RECOMMENDED P.C.B LAYOUT
 TOP VIEW

Material:

- Item ③ Male contact pin: Copper Tin plated
- Item ⑥ Terminal housing: Thermoplastic (UL94V-0)

Electrical:

cULus VDE /TUV

- Voltage rating: 300V/300V/300V
- Current rating: 20A/20A/20A
- Withstanding Voltage: 1.6 KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 

DIMENSION

Dim A	N×5.08
Dim B&C	(N-1)×5.08

N = Number of poles

Poles	Dim A	Dim B&C
2-6p	±0.15	±0.10
7-12p	±0.25	±0.15
13-18p	±0.30	±0.20
19-24p	±0.40	±0.30

PART NO.: 0Q xx 5 3 x 0 00J0 G

 No. of poles
 02 2 poles
 03 3 poles
 ...
 24 24 poles

 Body Color
 0 Black (RAL9005)
 2 Red (RAL3001/D)
 3 Orange(RAL2011/P)
 4 Yellow(RAL1018/A)
 5 Green(RAL6018/T)
 6 Blue (RAL5015/A)
 8 Grey(RAL7035/D)
 9 White(RAL1102)
 C Green(RAL6018/U)

 RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5✓	tolerance ASME Y14.5	projection 	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	MM	title
					angles X±0.5		TERMINAL BLOCK
					fillet X.X±0.3		PLUGGABLE SOCKET, OPEN TYPE, VERTICAL
					flat X*±1°	scale	dwg no
					dr HANKE FENG 040314		sheet 1 of 1 size
					enr HANKE FENG 040314		0Qxx53x000J0G
					chr SHI JUN 040314		A4
					appd SHI JUN 040314		type
							CUSTOMER Drawing
sheet index	revision	A					
	sheet	1					