

NOTES:

1. MATERIALS AND FINISHES:

BODY - BRASS, GOLD PLATING (.000003" MIN. THICK)
CONTACT - BeCu, GOLD PLATING (.000005" MIN. THICK)
INSULATOR - PTFE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 6 GHz
C. D.W.V: 1000 VRMS, MIN.

3. MECHANICAL:


A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65°C TO +165°C

4. BOARD THICKNESS=1.57 MM [.062"]


THIRD ANGLE PROJ.

REVISIONS




REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	01-Jul-16	01326	MZ



RECOMMENDED PCB LAYOUT



INTERFACE PER
CECC 22000
SERIES: MCX JACK



SCALE 8.000

CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ± 0.05mm ±0.1mm ±0.2mm ± 0.3mm ±1° NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	MATERIAL -	DRAWN M. ZHANG	DATE 01-Jul-16	TITLE MCX END LAUNCH JACK RECETP. (FOR .062" THICK PCB)		Amphenol RF www.amphenolrf.com		
		ENGINEER S. DUAN	DATE 01-Jul-16					
	REFERENCE SAME AS MCX625100-013-3GT30G-50 EXCEPT CENTER CONTACT PLATING CONFIGURATION LEVEL:	APPROVED S. HSIEH	DATE 06-Jul-16	SCALE: 10.0:1.0	SHEET	2 OF 2	DRAWING NO.	919-385J-51S
	FINISH	CAD FILE	DWG SIZE B		REV A	ITEM NO.	919-385J-51S	
						PART NO.	919-385J-51S	