

2310352-2 ✓ ACTIVE

TE Internal #: 2310352-2

10 Position Housing, Housing for Male Terminals, Wire-to-Board, 4 mm [.157 in] Centerline, Sealable, Black, Panel Mount

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings



Number of Positions: 10

Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: 1.5 mm [.06 in]

Connector System: **Wire-to-Board**

Centerline (Pitch): 4 mm [.157 in]

Features

Product Type Features

Connector Shape	Rectangular
Mixed & Hybrid Connector	No
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Board
Sealable	Yes
Primary Locking Feature	Integrated in Housing

Configuration Features

Number of Positions	10
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Size	1.5mm
Mating Tab Width	1.5 mm[.06 in]

Mechanical Attachment



Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Panel Mount

Housing Features

Centerline (Pitch)	4 mm [.157 in]
--------------------	----------------

Other

Connector Position Assurance Capable	No
--------------------------------------	----

Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (.23% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

10POS,060 SERIES,TAB HSG ASSY,SLD

English

CAD Files

Customer View Model

ENG_CVM_CVM_2310352-2_E.2d_dxf.zip

English

Customer View Model

2310352-2

10 Position Housing, Housing for Male Terminals, Wire-to-Board, 4 mm [.157 in]
Centerline, Sealable, Black, Panel Mount



[ENG_CVM_CVM_2310352-2_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2310352-2_E.3d_stp.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.