




Connectors > PCB Connectors > Backplane Connectors > Eurocard Connectors



Connector & Housing Type: **Plug**

Connector System: **Board-to-Board**

Termination Post & Tail Length: **3 mm [.118 in]**

Number of Positions: **64**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector & Housing Type	Plug
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board
DIN Size	Standard
DIN Level	II

Configuration Features

Number of Positions	64
Number of Rows	3
PCB Mount Orientation	Right Angle
Number of Columns	32
Rows Loaded	A, C
Number of Signal Positions	64

Contact Features

Contact Base Material	Copper Alloy
-----------------------	--------------



Contact Type	Pin
Termination Features	
Termination Post & Tail Length	3 mm[.118 in]
Mechanical Attachment	
Connector Mounting Type	Board Mount
Housing Features	
Housing Material	PBT GF30
Centerline (Pitch)	2.54 mm[.1 in]
Dimensions	
Connector Width	11.1 mm
Connector Height	11.1 mm
Connector Length	94 mm
Row-to-Row Spacing	2.54 mm[.1 in]
Usage Conditions	
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E84703
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.




Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 284259-E
STVR 64 FI AC VV 7-03 TL ** 247 E 172 *




TE Part # 284262-E
STVR 64 FI AC VV 7-03 EE ** 247 E 172 *




TE Part # 244294-E
STVC 64 F AC VV 7-00 EE 17,0 * 247 E007




TE Part # 244301-E
STVC 64 F AC VV 7-00 0606 13,0 * 247 E00




TE Part # 284979-E
STVC 64 F AC VV 7-00 TL 4,0 * 137 E007 1




TE Part # 244268-E
STVC 64 F AC VV 7-00 EE 4,0 * 247 E007 1




TE Part # 254120-E
STVC 64 F AC VV 7-00 EE 2,9 * 247 E007 1



TE Part # 284170-E
STVC 64 F AC VV 7-00 TL 2,5 * 247 E007 1



TE Part # 223839-E
STVC 64 F AC VV 7-00 TL 4,0 * 247 E007 1



TE Part # 224411-E
STVC 64 F AC VV 7-00 TL 4,0 * 247 E007 1

Customers Also Bought



TE Part #384295-E
STVE 160 M ABCDE VVVV 4-00 0606
** 247

TE Part #284259-E
STVR 64 FI AC VV 7-03 TL ** 247 E 172
*

TE Part #1SNG607016R0000
EP-LN-M40-LGR-A

TE Part #594751-E
STVH15 15 F ZD VV 2 TL 4,3 * 197 E
172 T

TE Part #3-825433-6
MOD 2 PINHDR 1X36P.

TE Part #925369-2
MOD 4 REC.HSG 1X02P

TE Part #1-1879417-4
CPF 0603 620K 0.1% 25PPM 1K RL

TE Part #5207826-4
HD-20 RCPT 9P VERT

TE Part #5787956-1
SOCKET ASSY IEEE1394

TE Part #1-1474654-1
FSN-22A-12

Documents

Product Drawings

STVC 64 M AC VV 4-00 0606 ** 247 E007 1

English

CAD Files

Customer View Model

ENG_CVM_CVM_364914-E_C.3d_igs.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_364914-E_C.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_364914-E_C.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

364914-E

Plug, Board-to-Board, 64 Position, 2.54 mm [.1 in] Centerline, Printed Circuit Board, 3 Row, Right Angle, 32 Column, Eurocard Connectors



Product Specification

English