

Materials

1. C3604 brass, nickel plated
2. C2680 brass, nickel plated
3. C3604 brass, nickel plated
4. POM, black

Electrical requirements

Dielectric strength: 1 min @ 500 Vac and 2mA
Insulation resistance: 100 M Ω @ 100 Vdc
Contact resistance: 50 m Ω or less

Mechanical requirements

Durability: 5000 mating cycles while maintaining normal operation and < 50m Ω
Bending strength: ≥ 1.5 kg
Breaking strength: ≥ 3.0 kg


Environmental tests

Salt spray test: 5% NaCl spray at 1ml/80cm²/h, chamber temp 46.5°C, spray temp 35°C, 87% humidity, 48 hours.
No oxidation.

Cold resistance: -25°C \pm 3 for 2 hours with no degradation.
Heat resistance: 85°C \pm 3 for 2 hours with no degradation.

Operating range

-30 to 85 °C



REVISION	DATE	DESCRIPTION	PREPARED:	NOTES	TENSILITY 20802 Sockeye Place #130 Bend, OR 97701 USA tel 541.323.3228 fax 541.323.4202 800 877.670.7118 www.tensility.com		
A	3/6/14	Initial release	JM 2014.03.06 11:17:12 -08'00'	RoHS compliant Function test: no open, no short circuit, no INT			
			VERIFIED: LA <small>Digitally signed by LA DN: cn=LA, o=Tensility, ou, email=L.A. (541) 323.4202 Date: 2014.03.06 12:41:06 -08'00'</small>		SIZE A PART NUMBER 50-00400		
			DIMENSIONS ARE IN MILLIMETERS				
			TOLERANCES: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	DESCRIPTION: Connector, stereo plug, 2.5xL19.6 mm, brass, nickel plated, molding style	SCALE: 3:1		
					WEIGHT:		SHEET 1 OF 1