




LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-




RECOMMENDED BEZEL CUT-OUT
SINGLE SIDED APPLICATIONS
SCALE 4:1



RECOMMENDED BEZEL CUT-OUT
BELLY TO BELLY APPLICATIONS




2340276-1
MOUNTED ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL




2340276-1
MOUNTED BELLY TO BELLY ON PC BOARD
SHOWN THRU RECOMMENDED BEZEL


THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN: IVAN TIAN 24JUL2018				TE Connectivity			
DIMENSIONS:				CHK: SEAN HAN 24JUL2018				NAME			
mm				APVD: SEAN HAN 24JUL2018				SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI SPRINGS, EXTENDED HEAT SINK			
				PRODUCT SPEC				SIZE			
				108-2364				CAGE CODE			
				APPLICATION SPEC				DRAWING NO			
				114-13120				RESTRICTED TO			
MATERIAL				WEIGHT				A100779C=2340276			
				FINISH				SCALE 6:1			
				CUSTOMER DRAWING				SHEET 2 OF 4			
								REV 1			



—CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)

4805 (3/11)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. 24JUL2018 DESIGNED BY: IVAN TIAN CHK. 24JUL2018 CHECKED BY: SEAN HAN APP'D. 24JUL2018 APPROVED BY: SEAN HAN		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm	0 PLC ±0.03 1 PLC ±0.1 2 PLC ±0.08 3 PLC ±0.05 4 PLC ±0.05 ANGLES FINISH	±0.03 ±0.1 ±0.08 ±0.05 ±0.05 ±1	SFP+ ENHANCED 1X2 CAGE ASSEMBLY, PRESS-FIT, EMI SPRINGS, EXTENDED HEAT SINK		
		PRODUCT SPEC 108-2364 APPLICATION SPEC 114-13120		SIZE CAGE CODE DRAWING NO. A1 00779 C 2340276	
MATERIAL		WEIGHT		RESTRICTED TO	
				-	
CUSTOMER DRAWING				SCALE 6:1 SHEET 4 OF 4 REV 1	