

MC9S12XB128MAA

(Not Recommended for New Designs)

16-bit MCU, S12X core, 128KB Flash, 66MHz, -40/+125degC, QFP 80

[Data Sheet](#)
[Product Summary](#)
[Software & Tools](#)
[Documentation](#)


Package :
[HQFP80](#)

plastic, thermal enhanced quad;
flat package; 80 terminals; 0.65
mm pitch; 14 mm x 14 mm x 2.3
mm body

[Buy Options](#) | [Operating Characteristics](#) | [Environmental Information](#) | [Quality Information](#) | [Shipping Information](#)

Operating Characteristics

Parameter	Value
Description	16-bit MCU, S12X core, 128KB Flash, 66MHz, -40/+125degC, QFP 80

Parameter	Value
Maturity	Product

Environmental Information

Material Declaration	PbFree	EU RoHS	Halogen Free	RHF Indicator	2nd Level Interconnect	REACH SVHC	Weight (mg)
MC9S12XB128MAA (935316956557)	Yes	Yes Certificate Of Analysis (CoA)	Yes	D	e3	REACH SVHC	935.5

Quality Information

Material Declaration	Safe Assure Functional Safety	Moisture Sensitivity Level (MSL)	Peak Package Body Temperature (PPT) (C°)	Maximum Time at Peak Temperatures (s)
		Lead Free Soldering	Lead Free Soldering	Lead Free Soldering
MC9S12XB128MAA (935316956557)	No	3	260	40

Shipping Information

Part Number	Harmonized Tariff (US) Disclaimer	Export Control Classification Number (US)
MC9S12XB128MAA (935316956557)	854231	3A991A2

ABOUT NXP

[Investors](#)
[Press, News, Blogs](#)
[Careers](#)

RESOURCES

[Mobile Apps](#)
[Contact Us](#)

FOLLOW US



News 26 Jul 2018



NXP Semiconductors Reports Second Quarter 2018 Results

[Read More](#)

