



**Circuit Board Indicators**

**Panel Mount Indicators**

**Solid State Lighting**

**Traffic Signals**

**Vehicle Lighting**

**Rail**

**Obstruction Lighting**

**Hazardous Area Lighting**

**Heliport Lighting**

**how to purchase**

[sales contacts](#)

[stock check](#)

[search](#)

[Product Line Search](#)

Please select a Product Line to search.

[Circuit Board Indicators](#)

[Find](#)

[Part # / Text Search](#)

**Part No.:**

**Text Search:**

[search](#)

[quick links](#)

**Dialight Corporate Video**

**Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp.** [View PDF File](#)

**Application Notes**  
**FAQs**

**Dialight Ltd (UK)**  
**Dialight Garufo**  
**Dialight BLP**  
**LumiDrives**

**Circuit Board Indicators - Through Hole Indicators**

P/N# **56807411114F**

3 mm Lens

Description	3 mm Quad X 4 Backlighting R/G-R/G-R/G-R/G
Package Options	5 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Quad Level Housing
Configuration	3 mm Lens
Viewing	Right Angle
Viewing Angle	60
Test Current (mA)	10mA

**Absolute Maximum Ratings** (Ta = 25 °)


Solder Temp	<b>260° for 5 sec</b>
Operating Temp	<b>-55 to +100° C</b>
Storage Temp	<b>-55 to +100° C</b>

**Distributor Stock Check**

Check stock with our distributors now.

56807411114F

[check stock](#)



RoHS / pB Free

[view PDF](#)

**Operating Characteristics**

LED Position	Found in position(s): 1-4
Color	Red / Green
Lamp Type	Bi-Color / Bi-Color
LED Type	
Intensity Min (mcd)	2.5 / 3.7
Intensity Typ (mcd)	4.7 / 10.0
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	621 / 569
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	100 / 100
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	