

Specification Sheet

Part Number: 156-02273

5 mm offset shifts bundle away from adjacent panels.

Oval fir tree prevents bundle rotation.

HellermannTyton's 4x design provides best in-class installation and extraction resistance for four common oval sizes.

Secure into wide range of panel thicknesses up to 6.75 mm, for application versatility.



2-Piece Cable Tie with Oval Fir Tree Mount, 5mm Offset, 4x Oval Hole FT, PA66HIRHSUV, Black, 3000/ctn

Article Number 156-02273

Type T50ROSSADFTOVALSET

Color Black (BK)

Quantity Per pack

Product Description These two-piece fasteners are pre-assembled and offer a simple and versatile method of bundling and mounting cables. Sold as an unassembled set, this oval fir tree and tie combination allows the user to install the tie in two different directions, securing the bundle perpendicular or inline to the oval mounting hole.

Short Description 2-Piece Cable Tie with Oval Fir Tree Mount, 5mm Offset, 4x Oval Hole FT, PA66HIRHSUV, Black, 3000/ctn

Global Part Name T50ROSSADFTOVALSET-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial) 50

Minimum Tensile Strength (Metric) 225

Fixation Method Fir Tree for oval holes

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Bundle Diameter Min (Imperial) 0.08

Bundle Diameter Min (Metric) 2.0

Bundle Diameter Max (Imperial) 1.97

Bundle Diameter Max (Metric) 50.0

Panel Thickness Min (Imperial) 0.02

Panel Thickness Max (Imperial) 0.27

Panel Thickness Min (Metric) 0.6

Panel Thickness Max (Metric) 6.75

Mounting Hole Diameter D (Imperial)	0.28 x 0.47 " 0.26 x 0.51 " 0.24 x 0.48 " 0.26 x 0.49 "
Mounting Hole Diameter D (Metric)	6.5 x 13.0 mm 6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 12.5 mm
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Foot Part Material	PA66HIRHSUV
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Operating Temperature intermittent, 1000 hours	+320°F (+160°C)
Operating Temperature intermittent, 5000 hours	+257°F (+125°C)
Operating Temperature intermittent, 500 hours	+329°F (+165°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000

Package Quantity (Metric) 3000

Customs Number 3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)