




Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Cavity Blanking Plug**

Operating Temperature Range: **-40 – 155 °C [-40 – 311 °F]**

Primary Product Color: **Black**

Primary Product Material: **Silicone**

Compatible Insulation Diameter Range: **2.4 – 3.2 mm [.094 – .126 in]**

Features

Product Type Features

Connector Seal & Plug Type	Cavity Blanking Plug
----------------------------	----------------------

Body Features

Primary Product Color	Black
Primary Product Material	Silicone

Dimensions

Compatible Insulation Diameter Range	2.4 – 3.2 mm [.094 – .126 in]
--------------------------------------	-------------------------------

Usage Conditions

Operating Temperature Range	-40 – 155 °C[-40 – 311 °F]
Operating Temperature (Max)	155 °C[311 °F]

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2025 (250)
Candidate List Declared Against: JUNE 2025 (250)
SVHC > Threshold:
Octamethylcyclotetrasiloxane (D4) (.37% in M-46177-1)

Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-EC7491-T273
[Econoseal Receptacles and Tabs](#)

TE Part # 1-968857-3
[AMP MCP 2.8, CONTACT SWS](#)

TE Part # CAT-M9194-CH8172
[Multilock Connector Housing](#)

Also in the Series | AMP MCP 2.8

[Automotive Connector Locks & Position Assurance\(8\)](#)

[Automotive Headers\(2\)](#)

[Automotive Housings\(226\)](#)

[Automotive Seals & Cavity Plugs\(2\)](#)



Connector Seals & Cavity Plugs(2)



Insertion & Extraction Tools(4)



Other Automotive Connector Accessories(2)

Customers Also Bought



TE Part #6-456402-8
CRIMPER, WIRE .055 "F"



CRIMPER REPRESENTATION ONLY

TE Part #3-1803224-5
CRIMPER, WIRE F



ANVIL REPRESENTATION ONLY

TE Part #2-1803512-2
ANVIL, COMBINATION



TE Part #2-2236706-3
2-POS. SEALED 2.8MM USCAR
CLEAN BODY FOR



ANVIL REPRESENTATION ONLY


TE Part #2391858-1
ANVIL, COMBINATION



CRIMPER REPRESENTATION ONLY

TE Part #8-1633713-7
CRIMPER, WIRE F PREMIUM

TE Part #3-1803767-5
CRIMPER, WIRE F



TE Part #5-1924513-4
GET 40 WAY HARNESS ASSY, KEY J



TE Part #2322231-5
40POS, HYBRID, REC HSG ASSY, SLD,
COD A

TE Part #2323834-1
POST, GUIDE, 5/8 X 5.5

Documents

Product Drawings

WIRE SEAL FOR ABS 25P(2.4-3.2)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_368941-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_368941-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_368941-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English