









OPTIONAL CONSTRUCTION



- NOTES
1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (2.3)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 3. (2.3)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL □ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	28
	LAST NO. USED	14

DWG STATUS				REVISION HISTORY				AUTH	DR	CK	APVD
DATE	STG	REV	CHG	N/P	ZONE						
230C01	R	003	-	-				REDRAWN TO PD & MAT'L SPEC WAS R006754B	216165	RH	RCH JH

DELPHI Automotive Systems			
MATERIAL SPEC M3592001 PA66 HS 1M BLK			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001			
PART DRAWING			
CODE NUMBER 6900	DWG DATE 08DE76	SCALE 2:1	D
OC SPEC	STYLE	VOLUME cm ³ 33.984	
PART GEOMETRY 3D SOLID		UNLESS OTHERWISE SPECIFIED: THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M - 1994 AS AMENDED BY THE GM GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DATUMS APPLY RFS. RULE #1 (PERFECT FORM AT MMC) DOES NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.	
COPY OF MATH DATA DO NOT SCALE	REFERENCE	DR	DATE
	BASE FUSBLK PAC/ON III		
METRIC UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS	THIRD ANGLE PROJECTION		
SHEET NUMBER 1 OF 1		DRAWING NUMBER 12004943	
DWG STATUS STG REV N/P R 003 -		SIZE A0	

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED		ANGULAR TOLERANCE ± 2°	
FROM	TO				
0	20	±0.15	±0.2	±0.4	±0.5
20	30	±0.2	±0.3	±0.4	±0.5
30	70	±0.3	±0.4	±0.5	±0.6
70	100	±0.4	±0.5	±0.6	±0.8
100	150	±0.5	±0.6	±0.8	±1.0
150	200	±0.6	±0.8	±1.0	±1.2
200	250	±0.8	±1.0	±1.2	±1.5
250	300	±1.0	±1.2	±1.5	±2.0
300	400	±1.2	±1.5	±2.0	±2.5