




**HARNESSING**

**HEAT SHRINK BOOTS**



✓ Active

TE CONNECTIVITY (TE)

**202A142-3/42-0**

Raychem | CAP , CRPS

202A142-3/42-0

TE Internal Number: 814728-000

Alias ID: 1196347-4

EU RoHS Compliant

EU ELV Compliant

Lipped No

Operating Temperature Range (°C) -20 – 60

Fluid/Chemical Resistance Suitable for occasional exposure to fluids

Adhesive Options /42 Precoat, -20 – 60°C (-4 – 140°F)

Material Systems Code 10

[↓](#) **PRODUCT DRAWING**  
English

## DOCUMENTATION

Product Drawings

**Boot, Straight, Overexpanded**

PDF

English

Product Environmental Compliance

Safety Data Sheet

**Aliphatic Polyamide Based Adhesives.**

PDF

Dutch

**Aliphatic Polyamide Based Adhesives.**

PDF

English

**Aliphatic Polyamide Based Adhesives.**

PDF

**French**

**Aliphatic Polyamide Based Adhesives.**

PDF

**German**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Italian**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Spanish**

**Aliphatic Polyamide Based Adhesives.**

PDF

**Swedish**

**Aliphatic Polyamide Based Adhesives.**

PDF

**English**

**EPS Heat Shrinkable Polymeric Products**

PDF

**French**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Italian**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Dutch**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Danish**

**EPS Heat Shrinkable Polymeric Products**

PDF

**English**

**EPS Heat Shrinkable Polymeric Products**

PDF

**German**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Norwegian**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Spanish**

**EPS Heat Shrinkable Polymeric Products**

PDF

**Swedish**

**FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

#### Product Type Features

**Molded Part Type** Molded Boot

---

#### Configuration Features

**Lipped** No

---

#### Body Features

**Material Systems Code** 10

**Adhesive Pre-Coat** Yes

**Material** Modified Polyolefin

---

#### Dimensions

**Cable Diameter Range** 7.4 – 25.4 mm [ .291 – 1 in ]

**Wire/Cable Outside Diameter** .3 in, .31 in, .35 in, .39 in, .43 in, .433 in, .47 in, .55 in, 10 mm, 11 mm, 12 mm, 14 mm, 8 mm, 9 mm

---

#### Usage Conditions

**Operating Temperature Range (°C)** -20 – 60

---

#### Operation/Application

**Power Cable Accessory** No

---

#### Industry Standards

**Government Qualified** No

**Approved Standards** BS-G-198-5-DA, DEF Std 59-97 Issue 3 Type DA, SAE AS I 81765/1, Type I, UL 224, File E85381

---

#### Other

**Fluid/Chemical Resistance** Suitable for occasional exposure to fluids

**Adhesive Options** /42 Precoat, -20 – 60°C (-4 – 140°F)

**Adhesive Type** General Purpose Pre-Coat Adhesive

---

#### Statement of Compliance

**Statement of Compliance**

PDF

---