

# Engine Start Stop Push Button Switches



90047

## Specifications

<b>Positions:</b>	2 Positions: Out (Open) - In (Momentarily Closed, Spring Return to Out)
<b>Housing:</b>	Diecast Zinc
<b>Circuitry:</b>	SPST
<b>Voltage Rating</b>	35A at 12V DC
<b>Mounting:</b>	Body through 0.04"-0.10" (1.0mm-2.5mm) Panel Hole

## Features and Benefits

- Silver Contacts for Corrosion Resistance
- Actuator resistant to oil, water and other liquids

## Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Transit and Commercial Vehicles

## Description

Littelfuse Push Pull Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The Engine Start-Stop Push Button Series provides temporary circuit closure to engage engine features. Interface designed for impact-resistance to ensure deliberate actuation.

## Web Resources

Download 2D print and technical resources at: [littelfuse.com/StartStopButtons](http://littelfuse.com/StartStopButtons)

## Ordering Information

PART NUMBER BULK	PART NUMBER RETAIL	DESCRIPTION	ACTUATOR	POSITIONS	TERMINATION
90047	90047-BP	Heavy Duty Engine Start-Stop Push Button	Black Button (Push, White 'ENGINE   START' Imprint)	2 Positions: Out (Open) - In (Momentarily Closed, Spring Return to Out)	2 Screws