TCO Series

Conductive Polymer Chip Capacitors (Standard)



FEATURES


- Ta-polymer technology
- High ripple capability
- High CV
- Surge robust
- J-lead LF

LEAD-FREE
LEAD-FREE COMPATIBLE COMPONENT

RoHS COMPLIANT

APPLICATIONS

- DC/DC
- Industrial
- Computers
- Telecom
- IoT
- Home applications




CASE DIMENSIONS:

millimeters

Code	EIA Code	EIA Metric	L±0.2	W₁±0.2	H±0.2	W₂±0.2	S±0.3
B	1210	3528-21	3.5	2.8	1.9	1.9	0.8

MARKING



HOW TO ORDER

TCO	B	1A	336	M	8R	-	□□□
Type	**Case Size** See table above	**Rated DC Voltage** 0E = 2.5Vdc 0J = 6.3Vdc 1A = 10Vdc 1C=16Vdc 1E=25Vdc	**Capacitance Code** pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)	**Tolerance** M = ±20%	**Packaging** 8 = Tape width R = Positive electrode on the side opposite to sprocket hole		**Discrimination code**

TECHNICAL SPECIFICATIONS

Technical Data:	All technical data relate to an ambient temperature of +25ºC
Capacitance Range:	15µF to 330µF
Capacitance Tolerance:	±20%
Leakage Current DCL:	Please see the ratings and part number reference table below
Temperature Range:	-55ºC to +105°C

Note: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges.
Please reference the KYOCERA AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance

The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

Downloaded from Arrow.com.

CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capacitance		Rated Voltage DC (V_R) @ 105°C					Cap Code
µF	Code	2.5V(e)	6.3V(j)	10V(A)	16V(C)	25V(E)	
15	156					100	e
22	226					90	j
33	336			150	100		n
47	476		150	150			s
100	107		35,45,150				ā
150	157		35,45,150				ē
220	227	35	35				j
330	337	35,45					n̄

Released ratings, (ESR ratings in mOhms)
Note: Voltage ratings are minimum values. KYOCERA AVX reserves the right to supply higher volage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

Part No.	Case Size	Capacitance (µF)	Rated Voltage (V)	Maximum Operating Temp. (°C)	DCL Max. (µA)	DF Max. (%)	ESR Max. @100kHz (mΩ)	100kHz RMS Current (mA) 45°C	MSL
2.5 Volt									
TCOB0E227M8R-EN1	B	220	2.5	105	55.0	8	35	1900	3
TCOB0E227M8R-EN2	B	220	2.5	105	55.0	8	35	1900	3
TCOB0E337M8R-EN1	B	330	2.5	105	82.5	15	35	1900	3
TCOB0E337M8R-EN2	B	330	2.5	105	82.5	15	35	1900	3
TCOB0E337M8R-ES1	B	330	2.5	105	82.5	15	45	1700	3
TCOB0E337M8R-ES2	B	330	2.5	105	82.5	15	45	1700	3
6.3 Volt									
TCOB0J476M8R	B	47	6.3	105	30.0	8	150	900	3
TCOB0J107M8R-EN1	B	100	6.3	105	63.0	8	35	1900	3
TCOB0J107M8R-EN2	B	100	6.3	105	63.0	8	35	1900	3
TCOB0J107M8R-ES1	B	100	6.3	105	63.0	8	45	1700	3
TCOB0J107M8R-ES2	B	100	6.3	105	63.0	8	45	1700	3
TCOB0J107M8R	B	100	6.3	105	63.0	8	150	900	3
TCOB0J157M8R-EN1	B	150	6.3	105	94.5	15	35	1900	3
TCOB0J157M8R-EN2	B	150	6.3	105	94.5	15	35	1900	3
TCOB0J157M8R-ES1	B	150	6.3	105	94.5	15	45	1700	3
TCOB0J157M8R-ES2	B	150	6.3	105	94.5	15	45	1700	3
TCOB0J157M8R	B	150	6.3	105	94.5	15	150	900	3
TCOB0J227M8R-EN1	B	220	6.3	105	139.0	15	35	1900	3
TCOB0J227M8R-EN2	B	220	6.3	105	139.0	15	35	1900	3
10 Volt									
TCOB1A336M8R	B	33	10	105	33.0	8	150	900	3
TCOB1A476M8R	B	47	10	105	47.0	8	150	900	3
16 Volt									
TCOB1C336M8R	B	33	16	105	159.0	10	100	1100	3
25 Volt									
TCOB1E156M8R	B	15	25	105	113.0	10	100	1100	3
TCOB1E156M8R-HB1	B	15	25	105	113.0	10	100	1100	3
TCOB1E226M8R-EB1	B	22	25	105	55.0	10	90	1200	3

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.
All technical data relates to an ambient temperature of +25C.

Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 1.5 volts.
DCL is measured at rated voltage after 5 minutes.
ESR allowed to move up to 1.25 times catalog limit post mounting.

NOTE: KYOCERA AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.


Downloaded from Arrow.com.

QUALIFICATION TABLE

TEST	TCO series (Temperature range -55°C to +105°C)				
	Condition		Characteristics		
Endurance	Apply rated voltage (Ur) at 105°C for 1000hrs through a serial resistence of ≤3.0Ω.		Visual examination	no visible damage	
			DCL	2x initial limit	
			ΔC/C	within ±20% of initial value	
			DF	1.5x initial limit	
Humidity	Store at 60±2°C, 90-95% relative humidity for 500 hours.		Visual examination	no visible damage	
			DCL	1.5x initial limit	
			ΔC/C	within +30/-20% of initial value	
			DF	1.5x initial limit	
Temperature Stability	Step / Temperature°C / Duration(min): 1 / -55 / 15; 2 / +105 / 15			-55°C	+105°C
			DCL	n/a	10xIL*
			ΔC/C	0/-20%	+80/0%
			DF	IL*	IL*
Surge Voltage	Apply 1.3x rated voltage (Ur) at 85±2°C for 1000 cycles, duration 6 min (30 sec charge, 5 min 30 sec discharge) through a charge / discharge resistance of 1000Ω.		Visual examination	no visible damage	
			DCL	initial limit	
			ΔC/C	±20% of initial limit	
			DF	initial limit	
Vibration	4.17 JIS C 5101-1 Frequency: 10 to 55 to 10Hz/min. Amplitude: 1.5mm Time: 2hours each in X and Y directions		Visual examination	no visible damage	
			DCL	initial limit	
			ΔC/C	within ± 5% of initial value	
			DF	initial limit	

*Initial Limit
For use outside of recommended conditions and special request, please contact KYOCERA AVX.


PACKAGING SPECIFICATIONS



Unit (mm)


Case	A±0.10	B±0.10	W±0.20	E±0.10	F±0.05	P1±0.10	P2±0.05	PO±0.10	DO+0.10/0	t1±0.05	t2±0.10	Standard packaging quantity
B	3.30	3.80	8.00	1.75	3.50	4.00	2.00	4.00	φ1.50	0.25	2.20	2,000 pcs

Polarity of parts: as indicated in the drawing below, the anodes (+) are at the right with respect to the direction of the tape pull out (on the opposite side to the feeding holes).



Downloaded from Arrow.com.

REEL DIMENSIONS



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

Downloaded from Arrow.com.