

Detailed information for: OBOC2000-24VDC

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

[Print...](#)
[Print to Pdf...](#)
[Data Sheet](#)
[Downloads](#)

OBOC2000-24VDC

General Information

Extended Product Type: OBOC2000-24VDC

Product ID: 1SNA645051R0400

EAN: 4013614508066

Catalog Description: OBOC2000-24VDC Optocoupler R600 2A,A1-A2=24VDC,MOS-FET

Long Description: Screw optocoupler OBOC1000 24vdc : 24vdc input / 5 upto 58vdc output 2A

Categories

Products » Low Voltage Products and Systems » Control Products » Electronic Relays and Controls » Interface Relays and Optocouplers



Ordering

Minimum Order Quantity: 10 piece

Customs Tariff Number: 85369095

Popular Downloads

Data Sheet, Technical Information: [1SVC117001D0200](#)

Instructions and Manuals: [1SVC645000M9000](#)

Dimensions

Product Net Width: 6 mm

Product Net Height: 67.5 mm

Product Net Depth / Length:	70 mm
Product Net Weight:	0.02 kg

Technical

Function:	Boxed optocoupler R600
Output:	solid-state output
Output Signal:	4.5 ... 58 V DC / 1 mA ... 2 A
Rated Control Supply Voltage (Us):	24 V DC
Terminal Type:	Screw Terminals

Environmental

RoHS Status:	Following EU Directive 2011/65/EU
--------------	-----------------------------------

Certificates and Declarations (Document Number)

CCC Certificate:	CCC_2017010303938926
CSA Certificate:	CSA_254821
cUR Certificate:	cUR_E352056
Declaration of Conformity - CE:	1SVD982016-0001
EAC Certificate:	EAC_RU_C-FR.ME77.B.01634
Instructions and Manuals:	1SVC645000M9000
LR Certificate:	LR_16_20068
RoHS Information:	1SVD982016-0001
UR Certificate:	UR_E352056

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	73 mm
Package Level 1 Height:	71 mm
Package Level 1 Depth / Length:	80 mm
Package Level 1 Gross Weight:	0.23 kg
Package Level 1 EAN:	3472596450519

Classifications

Object Classification Code:	K
ETIM 4:	EC001504 - Optocoupler
ETIM 5:	EC001504 - Optocoupler
ETIM 6:	EC001504 - Optocoupler
ETIM 7:	EC001504 - Optocoupler
eClass:	7.0 27371604