



PRODUCT NUMBER

PITCH

HAxx50x000J0G

2.54 mm



Dimension


DIM A	(N+1)×2.54
DIM B	(N-1)×2.54

N=Number of poles

POLES	Tolerance
2p-8p	±0.15
9p-12p	±0.25
13p-18p	±0.30
19p-24p	±0.40

PART NO.: HA xx 50 x 0 00J0 G

		Color	RoHS compliant
End stackable 0		Black (RAL9005)	(lead<4%)
No. of poles 2		Red (RAL3001/D)	In copper Alloy
02 2 poles 3		Orange(RAL2011/P)	
03 3 poles 4		Yellow(RAL1018/A)	
... .. 5		Green(RAL6018/T)	
24 24 poles 6		Blue (RAL5015/A)	
		8 Grey(RAL7004/P)	
		9 White(RAL1102)	
		C Multiple colors	

RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item①Terminal body:Thermoplastic (UL94V-0)
- Item②Terminal cover:Thermoplastic (UL94V-0)
- Item③Terminal lever:Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item④Female long contact: Brass Tin Plated.
- Item⑤Spring clamp: Stainless steel

Electrical cULus

- Voltage rating: 150VAC
- Current rating: 2A
- Wire range:
- Solid wire(AWG): 20-26
- Stranded wire(AWG): 20-26
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK													
ltr ecn no dr date				tolerances unless otherwise specified								title TERMINAL BLOCK SPRING CLAMP,90D WIRE INLET											
				angles		X.±0.5																	
				X.X±0.3																			
				X°±1°		X.XX±0.1		scale		dwg no sheet 1 of 1 size HAxx50x000J0G A4													
				dr		EVIN ZHONG 052314																	
				engr		EVIN ZHONG 052314																	
				chr		HANKE FENG 052314																	
				appd		SHI JUN 052314				type CUSTOMER Drawing													
sheet index		revision sheet		A 1																			