



Pushing Performance
Since 1945

Han-Mod_M_Mbit-Domino_4_F_I_CRT



Image is for illustration purposes only. Please refer to product description.

Part number	97 00 000 0413
Specification	Han-Mod_M_Mbit-Domino_4_F_I_CRT
HARTING eCatalogue	https://harting.com/97000000413

Identification

Category	Inserts
Type of module	Han® Megabit module
Description of the module	Insert

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	4
further contacts	+ shielding
Details	Please order crimp contacts separately. Please order Carrier Cube separately.
Details	Not suitable for hoods/housings low construction as well as Han-Modular® Eco, Han-Modular® Compact and Han-Modular® Twin.

Technical characteristics

Conductor cross-section (mm²)	0.14 ... 2.5 mm²
Wire outer diameter	≤3.5 mm
Rated current	10 A
Rated voltage	50 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V
Transmission characteristics	Cat. 5e Class D up to 100 MHz



Pushing Performance
Since 1945

Technical characteristics

Data rate	100 Mbit/s
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85389099
eCI@ss	27440205 Contact insert for industrial connectors