


LOC	DIST	REVISIONS				
DF	S0	P	LTR	DESCRIPTION	DATE	APVD
		D		REV PER ECO-05-002595	07-05	AA DE

1. TO MATE WITH AMP LGH-4 RECEPTACLE WITH 2.00 [50.8] BARREL DEPTH.
2. PIGTAIL IS SOLDER DIPPED.
3. MAX OPERATING VOLTAGE: 40 KVDC
4. INSULATION CUT, BUT NOT REMOVED.



4	5-867566-1
2	867566-1
REMARKS	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN C.C.THOMAS 12-AUG-96		tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608								
			CHK S.GLATFELTER 13-AUG-96												
DIMENSIONS: INCHES [mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD S.GLATFELTER 13-AUG-96		NAME								
		0 PLC ± -			PRODUCT SPEC		CABLE ASSY LGH-1 WITH LGH-4 MOLDED END -								
		1 PLC ± -			-										
		2 PLC ± .03 [0.8]			APPLICATION SPEC										
		3 PLC ± .015 [0.38]			-										
		4 PLC ± -					SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		
MATERIAL		FINISH			WEIGHT -		A2		00779		C=867566		-		
					CUSTOMER DRAWING					SCALE 2:1		SHEET 1 of 1		REV D	