




REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
C	PROPOSAL DRAWING	JUN19/08	L.CHAN
D	UPDATE LAYOUT	JUL18/18	L.CHAN



FRONT VIEW



SIDE VIEW





MATERIALS:

HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL94V-0
COLOR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.
50 MICRINCH [1.27 MICRONS] MIN. NICKEL OVERALL
100 MICRINCH [2.54 MICRONS] MIN. MATTE-TIN
OR GOLD FLASH OVER TAIL

SHIELD: COPPER ALLOY WITH NICKEL PLATED



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)
TOLERANCE: $\pm 0.002[0.05]$

LOCATE HOLES

 HOLE POSITIONS
 ARE BASIC

UNLESS SPECIFIED OTHERWISE		DRAWN	PAULW		MAY15/06		Amphenol Canada Corp. Commercial Products					
PRIMARY UNITS INCHES		CHECKED	CHIGOW		MAY15/06							
SECONDARY MILLIMETERS		M.E. APP'D				TITLE RJE06 SERIES, 8 POSITION 8 CONTACT, VERTICAL MOUNT, WITH SHIELD, AND FLANGE – RoHS COMPLIANT						
REFERENCE IN PARENTHESES		Q.A. APP'D										
GENERAL TOLERANCES		DWG APP'D										
1 DECIMAL PLACE ±0.015		ENG. REL. NO.										
2 DECIMAL PLACES ±0.010		REF.		EAR # A060504		DWG NO.		P-RJE06-188-1X20		REV D		
3 DECIMAL PLACES ±0.005		THIRD ANGLE PROJECTION				DO NOT SCALE DRAWING		CODE ID NO. 03554		DWG SIZE X	SCALE XX:1	SHEET 1 OF 1
ANGULAR DEGREES ±1.5°												