

2202158
<https://www.phoenixcontact.com/us/products/2202158>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Housing half shell (left), tall design, without vents, width: 6.3 mm, height: 99 mm, depth: 112.85 mm, color: gray (similar RAL 7042), cross connection: DIN rail bus connector (optional)

Your advantages

- Easy installation
- Variety of connection technology

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2202158 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC08 |
| Product key | ACHABZ |
| GTIN | 4055626004273 |
| Weight per piece (including packing) | 19.29 g |
| Weight per piece (excluding packing) | 16.994 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

ME MAX GEH-L G 3-3 GY - Housing half shell



2202158

<https://www.phoenixcontact.com/us/products/2202158>

Technical data


Notes

| | |
|----------------|---|
| Assembly note | Please observe the application note in the download area. |
| Recommendation | Material of contact pads for bus connector, galvanic gold (hard gold) |

Product properties

| | |
|------------------------------|---------------------|
| Product type | Housing half shells |
| Housing type | DIN rail housing |
| Housing series | ME-MAX |
| Product family | ME MAX.. G 3-3 |
| Number of rows | 3 |
| Ventilation openings present | no |

Dimensions

| | |
|---------------------------------|---|
| Dimensional drawing |  |
| Width | 6.3 mm |
| Height | 99 mm |
| Depth | 112.85 mm |
| Depth from top edge of DIN rail | 107 mm |

PCB design

| | |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

Material specifications

| | |
|--|-----------------|
| Color (Housing) | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 600 |
| Housing material | PA |
| Surface characteristics | untreated |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |

ME MAX GEH-L G 3-3 GY - Housing half shell



2202158

<https://www.phoenixcontact.com/us/products/2202158>

| | |
|---------------------------------------|------------------|
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

PCB data

| | |
|----------------------|-------------------|
| Type of PCB mount | Latching |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

ME MAX GEH-L G 3-3 GY - Housing half shell


2202158

<https://www.phoenixcontact.com/us/products/2202158>



Drawings

Dimensional drawing



Schematic view

ME MAX GEH-L G 3-3 GY - Housing half shell

2202158

<https://www.phoenixcontact.com/us/products/2202158>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2202158>



UL Recognized

Approval ID: E240868

ME MAX GEH-L G 3-3 GY - Housing half shell



2202158

<https://www.phoenixcontact.com/us/products/2202158>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME MAX GEH-L G 3-3 GY - Housing half shell



2202158

<https://www.phoenixcontact.com/us/products/2202158>

Environmental product compliance

| | |
|---|--|
| EU RoHS | |
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
| China RoHS | |
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |
| EU REACH SVHC | |
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com