






	1	2	3	4	5	6	7																																																																																			
A	YELLOW GREEN RED BLACK 				YELLOW GREEN RED BLACK 				A																																																																																	
B									B																																																																																	
C	 Conductor: [26AWG(0.16/7)Bare Copper]x4C Insulation: [PP6331 ID:0.95±0.03]x4C Jacket: PVC NOUL 65P Black Red Green Yellow 4.8 ± 0.2 2.4 ± 0.2 SEC:A-A				<table><tr><th>Part Number</th><th>Drawing Number</th><th>Wire Length "L"</th><th>Jacket Color</th><th>Cut Length</th></tr><tr><td>AT-K-S-26-4-S/7</td><td>A</td><td>2,135±30(7ft)</td><td>Silver</td><td>2,145-2,155mm</td></tr><tr><td>AT-K-S-26-4-S/14</td><td>B</td><td>4,270±60(14ft)</td><td>Silver</td><td>4,290-4,300mm</td></tr><tr><td>AT-K-S-26-4-S/25</td><td>C</td><td>7,625±100(25ft)</td><td>Silver</td><td>7,650-7,660mm</td></tr></table>				Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length	AT-K-S-26-4-S/7	A	2,135±30(7ft)	Silver	2,145-2,155mm	AT-K-S-26-4-S/14	B	4,270±60(14ft)	Silver	4,290-4,300mm	AT-K-S-26-4-S/25	C	7,625±100(25ft)	Silver	7,650-7,660mm	C																																																													
Part Number	Drawing Number	Wire Length "L"	Jacket Color	Cut Length																																																																																						
AT-K-S-26-4-S/7	A	2,135±30(7ft)	Silver	2,145-2,155mm																																																																																						
AT-K-S-26-4-S/14	B	4,270±60(14ft)	Silver	4,290-4,300mm																																																																																						
AT-K-S-26-4-S/25	C	7,625±100(25ft)	Silver	7,650-7,660mm																																																																																						
D									D																																																																																	
E	 A Cable tie: L=120mm, Silver				 B Cable tie: L=140mm, Silver				E																																																																																	
F									F																																																																																	
G	Unit: mm 				<table><tr><th>Scale</th><th>Free</th><th></th><th></th><th></th><th></th><th>Date</th><th>Name</th><th>Title</th></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>01.07.13</td><td>Wilson</td></tr><tr><td>X.</td><td>±X</td><td></td><td></td><td></td><td></td><td>Approved</td><td>01.07.13</td><td>Groll</td></tr><tr><td>X.X</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±X</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>Angle</td><td>TOL</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr></table>				Scale	Free					Date	Name	Title	TOLERANCE						Drawn	01.07.13	Wilson	X.	±X					Approved	01.07.13	Groll	X.X	±X								X.XX	±X								DIM	TOL								X.°	±X°								X.X°	±X°								Angle	TOL								G
Scale	Free					Date	Name	Title																																																																																		
TOLERANCE						Drawn	01.07.13	Wilson																																																																																		
X.	±X					Approved	01.07.13	Groll																																																																																		
X.X	±X																																																																																									
X.XX	±X																																																																																									
DIM	TOL																																																																																									
X.°	±X°																																																																																									
X.X°	±X°																																																																																									
Angle	TOL																																																																																									
H					 1940 W. Drake Drive, Suite 101 • Tempe, AZ 85283 Toll Free: 1-877-277-6266 • Email: info@assmann.us				Drawing-No. rev00 Sheet 1/1	H																																																																																
	1	2	3	4	5	6	7																																																																																			

Downloaded from [Arrow.com](https://arrow.com)