



Pushing Performance  
Since 1945

# Han DDD module, crimp male




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 017 3001
Specification	Han DDD module, crimp male
HARTING eCatalogue	<a href="https://harting.com/09140173001">https://harting.com/09140173001</a>

## Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® DDD module
Size of the module	Single module

## Version

Termination method	Crimp termination
Gender	Male
Number of contacts	17
Details	Please order crimp contacts separately.

## Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm²
Wire outer diameter	≤3.9 mm
Rated current	10 A
Rated voltage	160 V
Rated impulse voltage	2.5 kV
Pollution degree	3
Rated voltage acc. to UL	250 V
Insulation resistance	>10 <sup>10</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥10,000



**Pushing Performance**  
Since 1945

## Technical characteristics

Note on the mating cycles	Mating cycles with other HMC components
---------------------------	---

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 PVVA8.E318390
Approvals	DNV GL

## Commercial data

Packaging size	2
Net weight	4.5 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021167
eCl@ss	27440217 Module for industrial connectors (power/signals)
ETIM	EC000438
UNSPSC 24.0	39121552