



✓ Active

TE CONNECTIVITY (TE)

55A0111-24-0-1KF-US

Raychem | RC , SP

55A0111-24-0-1KF-US

TE Internal Number: CA4357-000

EU RoHS Compliant

EU ELV Compliant

Cable Type Spec 55

Voltage Rating (V) 600

Insulation Material Radiation-Crosslinked, Modified ETFE

Conductor Material Tin-Plated Copper

Wire Size (AWG) 24

 **PRODUCT DRAWING**

English

DOCUMENTATION

Product Drawings

Wire, Radiation-Crosslinked, Modified, ETFE-Insulated, Tin-Coated Copper, Lightweight

PDF [\(TIFF AVAILABLE\)](#)

English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Extruded, Modified, Fluoropolymer-Insulated Copper Or Copper Alloy

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 55

Cable Style Primary

Product Classification High Performance - Spec 44, 55 & RCW

Product Type Wire

Configuration Features

Number of Strands 19

Number of Conductors 1

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Insulation Material Radiation-Crosslinked, Modified ETFE

Conductor Material Tin-Plated Copper

Wire Color Black

Dimensions

Strand Size (AWG) 36

Wire Size (AWG) 24

Wire Size (mm²) .205

Conductor Diameter .64 mm [.025 in]

Overall Outside Diameter .94 mm [.037 in]

Insulation Thickness (in) .005

Wire Diameter .94 mm [.037 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 150

Other

Comment 1000 ft per spool ± 0 ft

Wire Source United States

PRODUCT COMPLIANCE



Statement of Compliance

[Statement of Compliance](#)

PDF
