





FCIconnect.com

Copyright FCI

form: A3

Downloaded from Arrow.com



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 0	D09P82C4GV00	D09P82C6GV00
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 0	D15P82C4GV00	D15P82C6GV00
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 0	D25P82C4GV00	D25P82C6GV00
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 0	D37P82C4GV00	D37P82C6GV00
Gold flash							0.76 μ gold	

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D +0.25 0	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15 0	D09P82C4GV00LF	D09P82C6GV00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15 0	D15P82C4GV00LF	D15P82C6GV00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25 0	D25P82C4GV00LF	D25P82C6GV00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25 0	D37P82C4GV00LF	D37P82C6GV00LF
Gold flash							0.76 μ gold	




view shown without plastic pin

Detail of grounding strip

PC card drilling dimensions(after plating)  
(thickness 1.60±0.20 mm)

## GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code —				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family D—SUB											
ltr	ecn no	dr	date	tolerances unless otherwise specified							title MALE CONNECTOR DELTA-D EUROSTYLE RIGHT ANGLED PRESS FIT										
G	ELX-I-18050	MP	2014/06/23	angles	linear	.0±.01															scale 2:1
						.00±.01															
				0°±2°		.000±.01															
				dr	PESSON		1995/10/13			dwg no					sheet 1 of 1			size			
				engr	MITHUN PAUL		2014/06/23			C01—8646—0387					A3						
				chr	ALIAS BABU		2014/06/23														
				appd	BIJU K PAUL		2014/06/23														
sheet index		revision sheet		G	1																

PDS: Rev :G

STATUS:Released

Printed: Jul 04, 2014