




Home> Products > MICRO SWITCH™ Sealed and High Accuracy Switches > AT > Product Page

66AT11-1



AT Series Toggle Switch, 6 pole, 3 position, Solder T2 type terminal, Standard Lever

Actual product appearance may vary.

Features

- Gold or silver contacts
- Choice of sealed bushing
- Standard or pull to unlock toggle lever
- Short behind-panel depth
- Solder or quick connect termination
- 2,4, 6, or 8 SPDT precision basic switches
- 2 or 3 position, momentary or maintained action

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Description

Compact multipole 2, 4, 6,or 8 SPDT design. MICRO SWITCH™ precision basic switches conserve space and weight. Pull -to-Unlock Toggle Levers prevent accidental operation: the lever must be pulled approximately 2,3 mm [0.09 inches] to change the positions. Many locking configurations are available. Lever to bushing seals. Hermetic basic switches are available. AT qualified versions meet MILS-8805/98. Various levers and styles are available.

Supporting Documentation

- Accessory: Lever Sleeve
- Accessory: Nuts
- Panel Cutout
- Engineering Drawing
- Accessory: Seals

Product Specifications	
Circuitry/Operating action	<div>Keyway Maintained      Center Maintained      Opposite Keyway Maintained</div> <div></div>
Product Type	MICRO SWITCH™ Toggle
Ampere/Voltage Range (Resistive Load)	0.1 A to 7.0 A at 0.5 Vdc to 28 Vdc
Circuitry	6PDT
Action	3 position
Mounting	Bushing 15/32 in
Termination	Solder T2 type
Comment	Contains SX basic switches
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	AT

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (\*) to expand search

Specification Search