



Part Number : [1300390370](#)

Product Description : DeviceNet Trunk Male Terminator Resistor with Mini-Change Connection, without LEDs, 5 Poles

Series Number : 130039

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : DN100




Documents and Resources

Drawings

[1300390370 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)4144-DC (27 June 2024) SCIP:7119006a-c416-47c7-ac77-d9b113636c15
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130039
Description	DeviceNet Trunk Male Terminator Resistor with Mini-Change Connection, without LEDs, 5 Poles
IP Rating	IP67
Product Name	DeviceNet Trunk
Type	Termination Resistor
UPC	78678869001

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	50V

Physical

Cable Diameter	N/A
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast

Material - Plating Mating	N/A
Net Weight	36.287/g
Orientation	Straight
Poles	5
Temperature Range - Operating	0° to +60°C
Wire Size (AWG)	N/A

This document was generated on Jun 13, 2026