Part Number : 1200660166
Product Description : Micro-Change (M12) Double-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Female (Straight), 22 AWG, Yellow PVC Cable, 1.0m (3.28') Length
Series Number : 120066
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 883030A09M010

Documents and Resources

Drawings

1200660166_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Female (Straight), 22 AWG, Yellow PVC Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78678826667

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	4.57mm (.180")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Yellow
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)

Downloaded from Arrow.com.

Coupling Style	Threaded
Gender	Female-Male
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	58.540/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 2661
Wire Size (AWG)	22

Downloaded from Arrow.com.