


Honeywell Sensing and Control

Search 

narrow your search

- Products
- Controls Monitoring and Lighting (354)
 - Machine Safety (1726)
 - Sensors (7074)
 - Switches (9814)

- Technology
- Control and Instrumentation (1063)
 - Electromechanical (9357)
 - Microstructure (2328)
 - Optical/Infrared (1077)
 - Thick Film (1764)
 - More...

Need Help?
Click here to contact us 

53C3200K Conductive Plastic Potentiometers
(Home : Products)



Actual product appearance may vary.

53 Series Industrial Potentiometer, Conductive Plastic Element, Solder lug Terminals, 2 W Power Rating, 200 kOhm Resistance Value

Sales & Service 

Distributor Inventory 

Overview Specs Documentation Application Notes

Product Specifications

| | |
|------------------------|--|
| Potentiometer Type | Industrial |
| Element Type | Conductive Plastic |
| Terminal | Solder lug |
| Power Rating | 2 W |
| Resistance Value | 200 kOhm |
| Resistance Tolerance | ± 10 % |
| Linearity | ± 5 % |
| Bushing Thread | 9,53 mm [0.375 in] x 32 NEF-2A |
| Bushing Length | 9,53 mm [0.375 in] |
| Bushing Type | Standard |
| Shaft Diameter | 6,35 mm [0.25 in] |
| Shaft Length | 22,23 mm [0.875 in] |
| Shaft Ending | Slotted |
| Body | 27.8 mm [1.094 in] diameter max. except at terminal standoff |
| Electrical Taper | Linear |
| Operating Temperature | -55 °C to 120 °C [-67 °F to 248 °F] |
| Working Voltage (Max.) | 500 V |
| Rotational Life | 25000 cycles |
| Mechanical Rotation | 312° |
| Availability | Global |
| Series Name | 53 |
| UNSPSC Code | 4111363300 |
| UNSPSC Commodity | 4111363300 Potentiometers |