


Part number description :

10134341-XXXLF

LF: Lead Free, RoHs compliant, see note

XXX : Color ref or/and version



Note : THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS PER GS-47-0004

TECHNICAL DATA / DIMENSIONS

Dimensions	
Width mm(in.)	5.0
Length mm(in.)	98.0
Height mm(in.)	37.5
Mounting type (EN 60715)	Omega TH35
Technical data	
Maximum load current	32A
Insulating material	PA
Self-extinguishing degree acc. to UL94	V0
Rated surge voltage	6kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal Voltage	630V
Nominal Current	24A
Connection data	
Conductor cross-section solid min/max	2.5 / 4 mm ²
Conductor cross-section stranded min/max	2.5 / 4 mm ²
AWG min/max	24-12AWG
Max conductor cross-section stranded with ferrule with plastic sleeve	2.5 mm ² / L=12 mm
Max conductor cross-section stranded with ferrule without plastic sleeve	4 mm ² / L=12 mm
Stripping length	max 12 mm

APPROVALS



AWG 24-12- 600V - 20A

EN60947-7-1 2.5mm² - 630V - 24A

ACCESSORIES


Item	Description
Marking	
10134397-001LF	Blank large marking tags for screwless terminals
10134419-001LF	Vertical marking tags

DIN RAIL system - Mounting and Installation material

10134392-001LF	Steel Omega Rail TH35x7,5mm -2mt length
10134393-001LF	Slotted Steel Omega Rail TH35x7,5mm -2mt length
10134394-001LF	Steel Omega Rail TH35x15mm -2mt length
10134395-001LF	Slotted Steel Omega Rail TH35x15mm -2mt length
10134387-001LF	Angled support bracket
10134389-001LF	End Bracket for TH35 Omega rail -Width 9mm
10134390-001LF	End Bracket for TH35 Omega rail -Width 6mm
10134391-001LF	Fast-snap End Bracket for TH35 Omega rail

Additional items

10134345-001LF	End Plate for Two Stage Screwless Terminal Block QD 2.5
10134273-001LF	Jumper bar 2 poles, pitch 5,1mm J2,5
10134273-002LF	Jumper bar 3 poles, pitch 5,1mm J2,5
10134273-003LF	Jumper bar 24 poles, pitch 5,1mm J2,5
10134271-001LF	Ratchet Cutting Tool for jumper bar J2,5 -orange
10134276-001LF	Red test plug adapter
10134276-002LF	Black test plug adapter



spec ref			dir	Aymeric Souidy	30-06-2015	projection			size	A3	scale	1:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED		eng	Aymeric Souidy	30-06-2015				ecn no				
			chr						rel level				
ISO 406		appr		Aymeric Souidy	30-06-2015	product family				DIN Terminal Block			
ISO 1101													
surface 	linear	0.X	± 0.3		title	Two stage Screwless Terminal Block QD 2,5			dwg no	10134341		rev	A
		0.XX	± 0.1										
		0.XXX	± 0.05										
	ISO 1302	angular	0°	± 2°	www.fcicom	cat. no.	-	Product customer drawing			sheet 1 of 1		