



**Part Number :** [2165712005](#)  
**Product Description :** Micro-Fit+ Vertical Header,  
Through Hole, 3.00mm Pitch, Single Row, 5 Circuits,  
0.38µm Gold (Au) Plating, Glow-Wire Capable, Black  
**Series Number :** 216571  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles

Documents and Resources

Drawings

[2165712005\\_sd.pdf](#)  
[2165710002-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)  
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2064600001-AS-000.pdf](#)  
[2064600000-PS-000.pdf](#)  
[2064600001-TS-000.pdf](#)  
[2157590005-TS-000.pdf](#)

Product Environment Compliance

Compliance

|                    |                                                                                                         |
|--------------------|---------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Compliant with Exemption 44; 34; 33                                                                     |
| China RoHS         |  per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                            |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                          |
| REACH SVHC         | Not Contained per D(2025)7771-DC (04 Feb 2026)                                                          |

|         |                           |
|---------|---------------------------|
| EU RoHS | Compliant per EU 2015/863 |
|---------|---------------------------|

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

|                |                                                                                                                                    |
|----------------|------------------------------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                                             |
| Category       | PCB Headers and Receptacles                                                                                                        |
| Series         | 216571                                                                                                                             |
| Description    | Micro-Fit+ Vertical Header, Through Hole, 3.00mm Pitch, Single Row, 5 Circuits, 0.38µm Gold (Au) Plating, Glow-Wire Capable, Black |
| Application    | Power, Wire-to-Board                                                                                                               |
| Component Type | PCB Header                                                                                                                         |
| Product Name   | Micro-Fit+                                                                                                                         |
| UPC            | 193264926800                                                                                                                       |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 12.5A |
|-------------------------------|-------|

|                   |                  |
|-------------------|------------------|
| Voltage - Maximum | 600V AC (RMS)/DC |
|-------------------|------------------|

## Physical

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 5                      |
| Circuits (maximum)             | 5                      |
| Color - Resin                  | Black                  |
| Durability (mating cycles max) | 200                    |
| First Mate / Last Break        | No                     |
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Keying to Mating Part          | No                     |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | High Copper Alloy      |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Matte Tin              |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.795/g                |
| Number of Rows                 | 1                      |
| Orientation                    | Vertical               |
| Packaging Type                 | Tray                   |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.57mm                 |
| PC Tail Length                 | 3.18mm                 |
| Pitch - Mating Interface       | 3.00mm                 |
| Pitch - Termination Interface  | 3.00mm                 |
| Plating min - Mating           | 0.381µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |
| Shrouded                       | Yes                    |
| Temperature Range - Operating  | -40° to +125°C         |
| Termination Interface Style    | Through Hole           |

## Solder Process Data

|              |    |
|--------------|----|
| Max-Duration | 30 |
|--------------|----|

|                              |          |
|------------------------------|----------|
| Lead-Free Process Capability | SMC&WAVE |
| Max-Cycle                    | 3        |
| Max-Temp                     | 260      |

---

## Mates With / Use With

### Mates with Part(s)

| Description                               | Part Number   |
|-------------------------------------------|---------------|
| Micro-Fit+ Single Row Receptacle Housings | <u>215759</u> |

---

This document was generated on Apr 11, 2026