



CONNECTOR HOUSINGS



Active

PRODUCT DRAWING
English

3D PDF



TE CONNECTIVITY (TE)
07P SL156 HSG W/LR W/O#5

647175-7
TE Internal Number: 647175-7

Always EU RoHS/ELV Compliant


Connector System Wire-to-Board

Centerline 3.96 mm [.156 in]

Number of Positions 7

Number of Rows 1

Housing Material Nylon 66/6



Product Drawings

HOUSING WITH LOCKING RAMP AND POLARIZING TABS, CIRCUIT NO. 5
CLOSED,SL-156

PDF
English

CAD Files

- 3D PDF
PDF
3D
- Customer View Model
2D_DXF.ZIP
English
- Customer View Model
3D_IGS.ZIP
English
- Customer View Model
3D_STP.ZIP
English

Product Specifications

Product Specification

[Hooded SL 156 Connectors, Tin](#)

PDF
English

[Hooded SL 156 Connectors, Gold](#)

PDF
English

[SL 156 Connectors](#)

PDF
English

Application Specification

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

PDF
English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

TIF
English

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

PDF
Japanese

[MTA 156 Ribbon Cable Connector Assemblies \(English And Spanish\)](#)

TIF
Japanese

[SL 156 Contacts And Housings](#)

PDF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Connector System	Wire-to-Board
	Connector Style	Receptacle
	Sealed	No
	Applies To	Printed Circuit Board
	Glow Wire Rating	Standard Part - Not Glow Wire
	Product Type	Connector
	Connector Type	Housing
Configuration Features	Number of Positions	7
	Number of Rows	1
	Selectively Loaded	Yes
	Preloaded	No
Electrical Characteristics	Operating Voltage (VAC)	250
Body Features	Sealable	No

Contact Features	Contact Type	Socket
	Contact Layout	Inline
	Shunts/Shorting Bars	Without
	Multiple Contact Types	Without
Mechanical Attachment	Panel Mount Retention	Without
	Panel Mount	Without
	Contact Retention	Without
Housing Features	Centerline	3.96 mm [.156 in]
	Housing Material	Nylon 66/6
	Housing Color	Natural
Dimensions	Length	27.68 mm [1.09 in]
	Height	16.76 mm [.66 in]
	Width	6.35 mm [.25 in]
Usage Conditions	Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
Operation/Application	Halogen Free	Yes
	Assembly Integration Feature	Without
	For Use With	Header
Identification Marking	Circuit Identification Feature	Without
Industry Standards	CSA Rating	Certified
	CSA File Number	LR7189
	UL Rating	Recognized
	CSA Certified	Yes
	VDE Tested	No
	UL File Number	E28476
	Agency/Standard	CSA, UL
	UL Flammability Rating	UL 94V-0
Packaging Features	Packaging Quantity	500

Product Compliance

Statement of Compliance
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)

