



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Mounting hardware Rack mounting brackets User manual Warranty card
--------------------	---

Physical

Colour	Black
Depth	63.7 cm
Height	8.9 cm
Net weight	43.09 kg
Width	43.2 cm

Input

Max line current	24 A
Input current limits	30 A
Load capacity	5000 VA
Plug standard	NEMA L6-30P
Input voltage	208 V

Output

Max current draw	24 A
Number of power socket outlets	12
Number of power socket outlets	12 NEMA 5-20R
Output voltage	120 V

Conformance

Product certifications	CSA
------------------------	-----

Standards	UL 1778
-----------	---------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	49.9 kg
Package 1 Height	25.4 cm
Package 1 width	62.2 cm
Package 1 Length	95.2 cm

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------