DIP switch

- DIP switch
- Operation switch
- Terminal block
- connector
- Healthcare
- Metal processed products
- DVMS
- Ultrasonic bonding technology

Domestic dealer
Overseas dealers

Slide K series

Click here to download PDF

スライド K シリーズ

特 長

1. オアテクニック・インプレッション増幅方式により安定して接触します。
2. 接触圧力は 200g/mm² 未満の「接触影響による接触作は しません。
3. 端子が直上形状ICとほぼ一致してできる、自動実装対象が 拡張されます。

名 称	仕 様
定格電流	DC5V 10mA
接触抵抗	50mΩ以下（初期）
絶縁抵抗	100MΩ以上
耐電圧	100V AC/1分
使用温度範囲	-25～+85℃
保存温度範囲	-30～+85℃
動作荷重	200g～300g
リフロー回数	2回

品名の呼称

記号	極 数	巾
K	スライド	
S	SMT	S
T	スルーホール	T

記号	極 数	巾
02	2	5
03	3	5
04	4	5
05	5	5
06	6	5
07	7	5
08	8	5
09	9	5
10	10	5
12	12	5

記号	端子形状
S	ガルタイプ
L	直角型

※上記標準品以外・カスタム品については お問合せください。

スライド K-1

スライド K シリーズ フロー実装

■ ダイナミック・インプレッション構造

■ 構造図

材料仕様

部 品 名	材	仕 上
ケース・ベース	耐熱樹脂 6-6ナイロン	黒 色
カバー	PPS	黒 色
ターミナル	銅 合 金	金メッキ
アクチュエータ	耐 熱 樹	黒メッキ

標準寸法

スライドタイプ
KSDシリーズ



フラッシュプラスライドタイプ
KSDシリーズ

品名及び寸法

品 名	極 数	L (mm)	A (mm)
KSD-02	2	4.5	
KSD-03	3	7.0	2.5
KSD-04	4	9.5	5.1
KSD-05	5	12.1	7.6
KSD-06	6	14.6	10.2
KSD-07	7	17.2	12.7
KSD-08	8	19.7	15.2
KSD-09	9	22.3	17.8
KSD-10	10	24.8	20.3
KSD-11	11	27.3	22.9
KSD-12	12	29.9	27.9

取付穴寸法

スライド K-2

スライド K シリーズ 面実装

■ ダイナミック・インプレッション構造

■ 構造図



材料仕様

部 品 名	材	仕 上
ケース・ベース	耐熱樹脂 6-6ナイロン	黒 色
カバー	PPS	黒 色
ターミナル	銅 合 金	金メッキ
アクチュエータ	耐 熱 樹	黒メッキ

標準寸法

スライドタイプ
KSDシリーズ面実装



フラッシュプラスライドタイプ
KSDシリーズ面実装

品名及び寸法

品 名	極 数	L (mm)	A (mm)
KSDT-02	2	4.5	---
KSDS-02	2	7.0	2.5
KSDS-03	3	9.6	5.1
KSDS-04	4	12.1	7.6
KSDS-05	5	14.6	10.2
KSDS-06	6	17.2	12.7
KSDS-07	7	19.7	15.2
KSDS-08	8	22.3	17.8
KSDS-09	9	24.8	20.3
KSDS-10	10	27.3	22.9
KSDS-11	11	29.9	25.4
KSDS-12	12	32.5	27.9

取付ランド寸法

スライド K-3

スライド K シリーズ

半田付について

■半田付条件

■半田リフロー条件

製品取扱上の注意

1. MLS用、ノブの位置はOFF になっています。単品→半田付→製為取込この段階を確認して下さい。
2. 洗浄液は、アルコール系、石油系、アニス油、臭素系溶剤が使用できます。但し、クルーバ系溶剤を御使用の場合は、弱ないご使用と多大ご注意、御確認ださ、御使用願います。

梱包箱・マガジン梱包数量

極数	スタンダード品	一般梱包数量	
	個当たり荷数量	ケース入数	梱包数
1	100個	4,000個	8,000個
2	80個	2,400個	3,600個
3	60個	1,400個	2,700個
4	50個	1,400個	2,000個
5	30個	1,200個	1,400個
6	25個	1,000個	1,400個
7	20個	800個	1,200個
8	20個	800個	1,200個
9	15個	600個	900個
10	15個	600個	900個
12	14個/個各極/4列	560個	840個

※1 梱包ケースサイズ（梱包箱）は 各極数とも同じです。
※2 梱包ケースサイズ（梱包箱）は 各極数とも同じです。

スライド K-4

3D CAD download

series	Product name	3D CAD	Remarks
K02	KSD12	download	Full pitch slide 1 pole flow mounting
	KSD22	download	Full pitch slide 2 pole flow mounting
	KSD32	download	Full pitch slide 3 pole flow mounting
	KSD42	download	Full pitch slide 4 pole flow mounting
	KSD52	download	Full pitch slide 5 pole flow mounting
	KSD62	download	Full pitch slide 6 pole flow mounting
	KSD72	download	Full pitch slide 7 pole flow mounting
	KSD82	download	Full pitch slide 8 pole flow mounting
	KSD92	download	Full pitch slide 9 pole flow mounting
	KSD102	download	Full pitch slide 10 pole flow mounting
	KSD122	download	Full pitch slide 12 pole flow mounting
	KSD125	download	Full pitch slide 1 pole mounting
	KSD225	download	Full pitch slide 2 pole mounting
	KSD325	download	Full pitch slide 3 pole mounting
	KSD425	download	Full pitch slide 4 pole mounting
	KSD525	download	Full pitch slide 5 pole mounting
	KSD625	download	Full pitch slide 6 pole mounting
	KSD725	download	Full pitch slide 7 pole mounting
	KSD825	download	Full pitch slide 8 pole mounting
	KSD925	download	Full pitch slide 9 pole mounting
	KSD1025	download	Full pitch slide 10 pole mounting
	KSD1225	download	Full pitch slide 12 pole mounting
K	KS12	download	Full pitch flat knob slide 1 pole flow mounting
	KS22	download	Full pitch flat knob slide 2 pole flow mounting
	KS32	download	Full pitch flat knob slide 3 pole flow mounting
	KS42	download	Full pitch flat knob slide 4 pole flow mounting
	KS52	download	Full pitch flat knob slide 5 pole flow mounting
	KS62	download	Full pitch flat knob slide 6 pole flow mounting
	KS72	download	Full pitch flat knob slide 7 pole flow mounting
	KS82	download	Full pitch flat knob slide 8 pole flow mounting
	KS92	download	Full pitch flat knob slide 9 pole flow mounting
	KS102	download	Full pitch flat knob slide 10 pole flow mounting
	KS122	download	Full pitch flat knob slide 12 pole flow mounting
K03	KS125	download	Full pitch flat knob slide 1 pole mounting
	KS225	download	Full pitch flat knob slide 2 pole mounting
	KS325	download	Full pitch flat knob slide 3 pole mounting
	KS425	download	Full pitch flat knob slide 4 pole mounting
	KS525	download	Full pitch flat knob slide 5 pole mounting
	KS625	download	Full pitch flat knob slide 6 pole surface mounting
	KS725	download	Full pitch flat knob slide 7 pole surface mounting
	KS825	download	Full pitch flat knob slide 8 pole mounting
	KS925	download	Full pitch flat knob slide 9 pole surface mounting
	KS1025	download	Full pitch flat knob slide 10 pole surface mounting
	KS1225	download	Full pitch flat knob slide 12 pole surface mounting

■ DIP switch tips

What is a DIP switch?

The official name of the DIP switch is DUAL IN LINE PACKAGE SWITCH. Unlike other switches, it is rarely mounted on the panel surface among operation switches, and it is a switch that is mounted on a printed circuit board and incorporated into an internal device. It is used for program setting, circuit switching, circuit check, etc. for the purpose of controlling electrical signals.

10 million monthly needs in Japan

DIP switch was born in the United States. In Japan, it has only been around for over 20 years since it first appeared as a switch for setting prices for vending machines. However, its use has expanded dramatically as a setting switch for programming, and it is said that there is currently a monthly demand for 10 million units in Japan.

Slide type that occupies nearly 70%

DIP switches are roughly divided into slide type, piano type, and rotary type according to the shape of the operation part, and are used properly according to the application, but the slide type is common and less than 70% of the total, mainly 4 poles and 8 poles. It is being used.

Copyright © Otax Co., Ltd. All Rights Reserved