# D-602-0126 ✔ ACTIVE


RAYCHEM

TE Internal #: 047703-000

Pin

View on TE.com >

Cable Assemblies > Data Bus Components > Data Bus Connectors



Contact Type: **Pin**

## Features

### Contact Features

| | |
|---|---|
| Contact Type | Pin |

### Termination Features

| | |
|---|---|
| Termination Method to Wire & Cable | Solder |

### Usage Conditions

| | |
|---|---|
| Operating Temperature (Max) | 125 °C[257 °F] |

## Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Compliant |
| EU ELV Directive 2000/53/EC | Not Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量超出标准 Restricted Substance(s) Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JUNE 2025 (250)<br>SVHC > Threshold:<br>Pb (.37% in Solder)<br>**Article Safe Usage Statements:**<br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer



Downloaded from Arrow.com.

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

## Compatible Parts




TE Part # 750984-004
10612-24-9

## Customers Also Bought



TE Part #050307-000
55A1122-22-9/96-9CS2275



TE Part #149657-000
B-020-20-N



TE Part #A47011-000
HW-254045-10-9



TE Part #518167-000
55A1832-16-MST3-9CS2275



TE Part #814507-000
222D232-4-0



TE Part #DT06-6S-EP11
PLG, 6P, BLK, N, SEAL RET, XCAP



TE Part #8-1437621-7
KFS500B1/4=KNOB ALUM BLACK ANO

TE Part #EM5558-000
D-600-2932



Downloaded from Arrow.com.

TE Part #EM5555-000
D-600-2929

TE Part #2294964-2
CIRCULAR HD, RECEPTACLE, FREE HANGING

## Documents

### Product Drawings

D-602-0126

English

### Datasheets & Catalog Pages

Data Bus Components Brochure

English

### Product Specifications

Termination Procedure for 748 Series SolderTacts Contacts for Twisted Pair Cable D-602-0126, D-602-0127

SolderTact Military-Grade Electrical Contacts for Solder Termination

English



Downloaded from Arrow.com.