








Leiterplatten-Layout Vorschlag für SMT
PCB-Layout Proposal for SMT



Anforderungsstufe 1
Performance Level 1


Kontaktbereich vergoldet
Mating Area gold plating

Anschlussbereich verzinkt 4-6 µm
Terminal Area 4-6 µm tin plating


Koplanarität der Anschlüsse ≤ 0,1 mm
Coplanarity Area of Termination ≤ 0,1 mm


454207-E		weiß white	0,6	6,6	1,2	6,0	Codierung wie Variante schwarz Encoding such variant black
254710-E		rot red	4,2	3,0	4,8	2,4	
254709-E		grün green	3,0	4,2	3,6	3,6	
254708-E		blau blue	1,8	5,4	2,4	4,8	
254707-E		schwarz black	0,6	6,6	1,2	6,0	
Ident-Nr. part-no.	Codierung coding	Farbe color	A	B	C	D	Bemerkung note

Verpackt in Gurtverpackung
Tape on Reel Packaging
Verpackungseinheit: 320 Stück
Packaging unit: 320 pcs



Abspulrichtung - Reel off Direction



Information:			Tolerances		Scale 3:1	
			 All Dimensions in mm			
<u>Customer drawing:</u> THIS DRAWING IS A CONTROLLED DOCUMENT.			Subject to modification without prior notice. Drawing will not be updated.		Designation	
					ERNI-M 2,54 SRC-P, 6-polig	
			 TE Connectivity		C- 224915-E	
h		30.04.2013			1	
Index		Date			A2	
					Class SRCP	

Copyright by TE GmbH
Proprietary notice pursuant to ISO 16151 to be observed