



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

2N6284 (NPN) Silicon Complementary Darlington Transistors Power Amplifier

Description:

The 2N6284 (NPN) is a silicon complementary Darlington transistor in a TO3 type case designed for general-purpose amplifier and low-frequency switching applications.

Features:

- High DC Current Gain @ $I_C = 10A$:
 $h_{FE} = 2400$ Typ
- Collector-Emitter Sustaining Voltage: $V_{CEO(sus)} = 100V$ Min
- Monolithic Construction with Built-In Base-Emitter Shunt Resistors

Absolute Maximum Ratings: ($T_A = +25^\circ C$ unless otherwise specified)

Collector-Emitter Voltage, V_{CEO}	100V
Collector-Base Voltage, V_{CB}	100V
Emitter-Base Voltage, V_{EB}	5V
Collector Current, I_C	
Continuous	20A
Peak	40A
Base Current, I_B	0.5mA
Total Power Dissipation ($T_C = +25^\circ C$), P_D	160W
Derate Above $25^\circ C$	0.915W/ $^\circ C$
Operating Junction Temperature Range, T_J	-65° to $+200^\circ C$
Storage Temperature Range, T_{stg}	-65° to $+200^\circ C$
Thermal Resistance, Junction-to-Case, R_{thJC}	1.09 $^\circ C/W$

Electrical Characteristics: ($T_A = +25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF Characteristics						
Collector–Emitter Sustaining Voltage	$V_{\text{CEO(sus)}}$	$I_C = 100\text{mA}, I_B = 0$	100	–	–	V
Collector Cutoff Current	I_{CEO}	$V_{\text{CE}} = 50\text{V}, I_E = 0$	–	–	1.0	mA
	I_{CEX}	$V_{\text{CE}} = 100\text{V}, V_{\text{BE(off)}} = 1.5\text{V}$	–	–	0.5	mA
		$V_{\text{CE}} = 100\text{V}, V_{\text{BE(off)}} = 1.5\text{V}, T_A = +150^{\circ}\text{C}$	–	–	5.0	mA
Emitter Cutoff Current	I_{EBO}	$V_{\text{BE}} = 5\text{V}, I_C = 0$	–	–	2.0	mA
ON Characteristics (Note 1)						
DC Current Gain	h_{FE}	$V_{\text{CE}} = 3\text{V}, I_C = 10\text{A}$	750	–	18000	
		$V_{\text{CE}} = 3\text{V}, I_C = 20\text{A}$	100	–	–	
Collector–Emitter Saturation Voltage	$V_{\text{CE(sat)}}$	$I_C = 10\text{A}, I_B = 40\text{mA}$	–	–	2.0	V
		$I_C = 20\text{A}, I_B = 200\text{mA}$	–	–	3.0	V
Base–Emitter Saturation Voltage	$V_{\text{BE(sat)}}$	$I_C = 20\text{A}, I_B = 200\text{mA}$	–	–	4.0	V
Base–Emitter ON Voltage	$V_{\text{BE(on)}}$	$V_{\text{CE}} = 3\text{V}, I_C = 10\text{A}$	–	–	2.8	V
Dynamic Characteristics						
Small–Signal Current Gain	h_{fe}	$V_{\text{CE}} = 3\text{V}, I_C = 10\text{A}, f = 1\text{kHz}$	300	–	–	
Magnitude of Common Emitter Small–Signal Short–Circuit Forward Current Transfer Ratio	$ h_{\text{fe}} $	$V_{\text{CE}} = 3\text{V}, I_C = 10\text{A}, f = 1\text{MHz}$	4.0	–	–	MHz
Output Capacitance	C_{ob}	$V_{\text{CB}} = 10\text{V}, I_E = 0, f = 0.1\text{MHz}$	–	–	400	pF

Note 1. Pulse Test: Pulse Width = 300 μs , Duty Cycle = 2%



