





9	8	7	6	5	4	3	2	1
PART NUMBER		DESCRIPTION			MATERIAL			AGENCY APPROVAL
180414-0102		COB LED HOLDER 13.5MM X 13.5MM			POLYAMIDE (PA66) GLASS FILLED, COLOR: NATURAL			UL496 FILE E345583
180414-0112		COB LED HOLDER 13.5MM X 13.5MM			POLYESTER (PBT) GLASS FILLED, COLOR: WHITE			UL496 FILE E345583
180414-0202		COB LED HOLDER 13.5MM X 13.5MM WITH TAB CAP			POLYAMIDE (PA66) GLASS FILLED, COLOR: NATURAL			UL496 FILE E345583
180414-0212		COB LED HOLDER 13.5MM X 13.5MM WITH TAB CAP			POLYESTER (PBT) GLASS FILLED, COLOR: WHITE			UL496 FILE E345583

HOLDER ASSEMBLY
180414-0102, 180414-0112



ISO VIEW 1
SCALE 1:1

NOTES:

1. MATERIALS: HOUSING AND CAPS: SEE CHART, TERMINAL: COPPER ALLOY
2. FINISHES: TERMINAL: NICKEL (Ni) UNDERPLATE 1.27 µm, WIRE TRAP SELECT TIN (Sn) 2.54µm, LED CONTACT SELECT GOLD (Au) 0.76µm
3. PRODUCT SPECIFICATION: PS-180414-001
4. PACKAGING SPECIFICATION: PK-180419-005
5. SEE CHART FOR AGENCY APPROVAL INFORMATION
6. ELV AND ROHS COMPLIANT.
7. SEE SHEET 3 FOR APPLICATION NOTES.

9

8

7

6

5

4

3

2

1

E

E

D

D

C

C

B




B

A


A

HOLDER ASSEMBLY WITH TAB CAP


180414-0202, 180414-0212



PART MARKED WITH
DATE CODE (YYWWD)
MFG PLANT (CD)
REVISION (X)
PART NUMBER (180414-02X2)



ISO VIEW2
SCALE 1:1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS		SCALE	CURRENT REV DESC:				molex			
mm		1:1								
GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 603651 DRWN: SCHEN76 2018/08/22 CHK'D: BPISZCZOR 2018/08/30 APPR: BPISZCZOR 2018/08/30				COB LED HOLDER ASSEMBLY 13.5MM X 13.5MM SQUARE			
ANGULAR TOL ± 0.5 °										
4 PLACES ±										
3 PLACES ±			INITIAL REVISION: DRWN: MCOLE 2012/05/24 APPR: DMCGOWAN 2012/08/06				PRODUCT CUSTOMER DRAWING DOCUMENT NUMBER SD-180414-102 DOC TYPE PSD DOC PART 001 REVISION C3			
2 PLACES ± 0.13										
1 PLACE ± 0.25										
0 PLACES ±										
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIRD ANGLE PROJECTION		DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER	SHEET NUMBER
					A3-SIZE	180414			GENERAL MARKET	2 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2018/08/30	01:43:45
-----------------	----	--------------	------------	----------

8

7

6

5


4

3


2

1

9	8	7	6	5	4	3	2	1
COB MFG		TYPE		DIM 'X'	DIM 'Y'	DIM 'Z'	DIM 'D'	
CITIZEN		CLL020, CLL022, CLU024, CLU026, CLU028		13.5	13.5	0.90	11.2	
TRIDONIC		SLE G5 LES10		13.5	13.5	0.90	9.4	
SEOUL		ZC6		13.5	13.5	0.90	10.0	
CITIZEN		CLU025, CLU027		13.5	13.5	0.90	7.4	
CITIZEN		CLU700, CLU701		13.5	13.5	0.90	7.8	
EVERLIGHT		EAHP1313WA*, EAHP1313WB*, EAHP1313WC*		13.5	13.5	0.90	10.8	
EVERLIGHT		EA1313 36V/3W		13.5	13.5	0.90	10.8	
EVERLIGHT		EA1313 36V/6W		13.5	13.5	0.90	10.8	
EVERLIGHT		EA1313 36V/10W		13.5	13.5	0.90	10.8	
EVERLIGHT		EA1313 36V/13W		13.5	13.5	0.90	10.8	
VOSSLOH-SCHWABE		DMC122C		13.5	13.5	1.00	10.0	
BRIDGELUX		GEN7. V10		13.5	13.5	1.00	10.65	



- NOTES:
1. APPLICATION SPECIFICATION: AS-180412-001
 2. FOR USE WITH: 13.5 MM X 13.5 MM COB
 3. WIRE GAUGE: 18, 20 AND 22 AWG, SOLID OR STRANDED WITH TIN OVERCOAT. STRIP LENGTH 10MM +2.0/-0.0MM. RECOMMENDED MAXIMUM DIAMETER AFTER TINNING: 1.40MM. LARGER DIAMETER WIRES ARE ACCEPTABLE IF FULLY INSERTABLE IN WIRE TRAP AND NO WITHDRAWAL WITHIN 20N FORCE.
 4. IF REWORK IS REQUIRED, WIRE MUST BE REPLACED WITH SAME AWG AND TYPE. CARE MUST BE TAKEN NOT TO DAMAGE WIRE TRAP. REWORK IS ACCEPTABLE IF WIRE IS FULLY INSERTABLE IN WIRE TRAP AND NO WITHDRAWAL WITHIN 20N FORCE.



RECOMMENDED MOUNTING DIMENSION IS


WIRES ARE ACCEPTABLE IF FULLY INSERTABLE IN WIRE TRAP AND NO WITHDRAWAL WITHIN 20N FORCE.

4. IF REWORK IS REQUIRED, WIRE MUST BE REPLACED WITH SAME AWG AND TYPE. CARE MUST BE TAKEN NOT TO DAMAGE WIRE TRAP. REWORK IS ACCEPTABLE IF WIRE IS FULLY INSERTABLE IN WIRE TRAP AND NO WITHDRAWAL WITHIN 20N FORCE.

DOCUMENT STATUS	P1	RELEASE DATE	2018/08/30	01:43:45
-----------------	----	--------------	------------	----------




THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex	
mm		1:1							
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 603651 DRWN: SCHEN76 2018/08/22 CHK'D: BPISZCZOR 2018/08/30 APPR: BPISZCZOR 2018/08/30				COB LED HOLDER ASSEMBLY 13.5MM X 13.5MM SQUARE	
ANGULAR TOL ± 0.5 °									
4 PLACES		±		INITIAL REVISION: DRWN: MCOLE 2012/05/24 APPR: DMCGOWAN 2012/08/06				PRODUCT CUSTOMER DRAWING	
3 PLACES		±							
2 PLACES		± 0.13		DOCUMENT NUMBER SD-180414-102				DOC TYPE PSD	
1 PLACE		± 0.25							
0 PLACES		±		SHEET NUMBER 3 OF 3					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									
THIRD ANGLE PROJECTION		DRAWING		SERIES		CUSTOMER GENERAL MARKET			
		A3-SIZE		180414					

10	9	8	7	6	5	4	3	2	1
PART NUMBER	DESCRIPTION		POCKET DEPTH	HOUSING	TERMINAL	CAP			
180414-1112	COB LED HOLDER ASSEMBLY		0.90	180413-1112	180155-0133	180154-0105			
180414-2112	COB LED HOLDER ASSEMBLY		0.75	180413-2112	180155-0133	180154-0105			



ISO VIEW 1
SCALE 1:1




P/N 180414-1112 HOLDER ASSEMBLY
(0.90 POCKET DEPTH)




- NOTES:
1. MATERIALS: HOUSING AND CAPS: POLYESTER PBT GLASS FILLED; COLOR: WHITE; TERMINAL: COPPER ALLOY
 2. FINISHES: TERMINAL CONTACT: SELECT GOLD OVER NICKEL WIRE TRAP: SELECT TIN OVER NICKEL
 3. PRODUCT SPECIFICATION: 180414-0000-PS
 4. PACKAGING SPECIFICATION: PK-180419-005
 5. UL:0LFB2 UL496 FILE NO. E345583
 6. ELV AND ROHS COMPLIANT
 7. FOR USE WITH: 13.5 MM X 13.5 MM COB LED
 8. WIRE GAUGE: 18, 20, AND 22 AWG, SOLID OR STRANDED WITH TIN OVERCOAT. STRIP LENGTH 10MM +2.0/-0.0MM.
 9. ALL DIMENSIONS IN PARENTHESES (XX.XX) ARE FOR REFERENCE ONLY

ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZABJANOVSKI 2017/02/21 CHKD: APPR: BPI/SZCZOR 2017/03/07		DESCRIPTION	REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
					mm INCH		DRAWN BY MCOLE	DATE 2013/12/09	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE						
							CHECKED BY	DATE							
							MCOLE	2013/12/09							
							APPROVED BY	DATE	molex						
							DMCGOWAN	2013/12/09							
							MATERIAL NO.	DOCUMENT NO.						SHEET NO.	
							SEE CHART		SD-180414-112		1 OF 5				
							SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								

P/N 180414-2112 HOLDER ASSEMBLY
(0.75 POCKET DEPTH)



ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZAB JANOVSKI 2017/02/21 CHKD: APPR: BPI / SZCZOR 2017/03/07 REV	QUALITY SYMBOLS F_A=0 F_B=0 F_C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE			
		4 PLACES	± ---	± ---	MCOLE	2013/12/09				
		3 PLACES	± ---	± ---	CHECKED BY	DATE				
		2 PLACES	± 0.13	± ---	MCOLE	2013/12/09	DOCUMENT NO. SD-180414-112			
		1 PLACE	± 0.25	± ---	APPROVED BY	DATE				
		0 PLACE	± ---	± ---	DMCGOWAN	2013/12/09	SHEET NO. 2 OF 5			
		ANGULAR ±1/2°		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				




RECOMMENDED MOUNTING DIMENSIONS

ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZABJANOVSKI 2017/02/21 CHKD: APPR: BPI SZCZOR 2017/03/07	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE		
				4 PLACES	± ---	± ---	MCOLE	2013/12/09			
				3 PLACES	± ---	± ---	CHECKED BY	DATE	molex		
				2 PLACES	± 0.13	± ---	MCOLE	2013/12/09			
				1 PLACE	± 0.25	± ---	APPROVED BY	DATE	DOCUMENT NO. SD-180414-112		
				0 PLACE	± ---	± ---	DMCGOWAN	2013/12/09			
				ANGULAR ±1/2°		MATERIAL NO.		SHEET NO.			
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		3 OF 5			
						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

10	9	8	7	6	5	4	3	2	1
COB MFG	TYPE	DIM 'X'	DIM 'Y'	DIM 'Z'	DIM 'D'	OFFSET			
VOSSLOH-SCHWABE	DMC122C	13.5	13.5	1.0	10.0	0.10			


ILLUSTRATION OF P/N 180414-1112 HOLDER MATED WITH LED



ENTER DESCRIPTION EC NO: SSL2017-0024 DRWNL: ZABJANOVSKI 2017/02/21 CHKD: BPTISZCZOR 2017/03/07 APPR: BPTISZCZOR 2017/03/07 C4		DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			F _A =0	mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE				
			F _G =0	4 PLACES ± ---	± ---	MCOLE	2013/12/09					
			F _P =0	3 PLACES ± ---	± ---	CHECKED BY	DATE	DOCUMENT NO. SD-180414-112				
				2 PLACES ± 0.13	± ---	MCOLE	2013/12/09					
				1 PLACE ± 0.25	± ---	APPROVED BY	DATE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
				0 PLACE ± ---	± ---	DMCGOWAN	2013/12/09					
			ANGULAR ±1/2°		MATERIAL NO.		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
			SIZE B									


	10	9	8	7	6	5	4	3	2	1
	COB MFG	TYPE			DIM 'X'	DIM 'Y'	DIM 'Z'	DIM 'D'	OFFSET	
	CITIZEN	CLL020, CLL022, CLU024, CLU026, CLU028			13.5	13.5	0.90	11.2	0.15	
F	SEOUL	ZC6			13.5	13.5	0.90	10.0	0.15	
	TRIDONIC	SLE G5 LES10			13.5	13.5	0.90	9.4	0.15	
	CITIZEN	CLU025, CLU027			13.5	13.5	0.90	7.4	0.15	
	CITIZEN	CLU700, CLU701			13.5	13.5	0.90	7.8	0.15	
	EVERLIGHT	EAHP1313WA*, EAHP1313WB*, EAHP1313WC*			13.5	13.5	0.90	10.8	0.15	
	EVERLIGHT	EA1313 36V/3W			13.5	13.5	0.90	10.8	0.15	
E	EVERLIGHT	EA1313 36V/6W			13.5	13.5	0.90	10.8	0.15	
	EVERLIGHT	EA1313 36V/10W			13.5	13.5	0.90	10.8	0.15	
	EVERLIGHT	EA1313 36V/13W			13.5	13.5	0.90	10.8	0.15	
	VOSSLOH-SCHWABE	DMC122C			13.5	13.5	1.00	10.0	0.25	

ILLUSTRATION OF P/N 180414-2112 HOLDER MATED WITH LED




DETAIL 2
SCALE 4:1

SECTION W-W






ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: SSL2017-0024		F=0		mm		MM ONLY		2:1		METRIC		⊙	
DRAWN: ZABJANOVSKI 2017/02/21		F=0		INCH		DRAWN BY DATE		TITLE		COB LED HOLDER ASSEMBLY			
CHKD: BPTISZCZOR 2017/03/07		F=0		4 PLACES ± --- ± ---		MCOLE 2013/12/09		CHECKED BY DATE		13.5 MM X 13.5 MM SQUARE			
APPR: BPTISZCZOR 2017/03/07		F=0		3 PLACES ± --- ± ---		MCOLE 2013/12/09		APPROVED BY DATE					
		F=0		2 PLACES ± 0.13 ± ---		DMCGOWAN 2013/12/09		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				1 PLACE ± 0.25 ± ---		SEE CHART				SD-180414-112		5 OF 5	
				0 PLACE ± --- ± ---									
				ANGULAR ± 1/2°									
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

10	9	8	7	6	5	4	3	2	1
PART NUMBER	DESCRIPTION		POCKET DEPTH	HOUSING	TERMINAL	CAP			
180414-1112	COB LED HOLDER ASSEMBLY		0.90	180413-1112	180155-0133	180154-0105			
180414-2112	COB LED HOLDER ASSEMBLY		0.75	180413-2112	180155-0133	180154-0105			



ISO VIEW 1
SCALE 1:1




P/N 180414-1112 HOLDER ASSEMBLY
(0.90 POCKET DEPTH)




- NOTES:
1. MATERIALS: HOUSING AND CAPS: POLYESTER PBT GLASS FILLED; COLOR: WHITE; TERMINAL: COPPER ALLOY
 2. FINISHES: TERMINAL CONTACT: SELECT GOLD OVER NICKEL WIRE TRAP: SELECT TIN OVER NICKEL
 3. PRODUCT SPECIFICATION: 180414-0000-PS
 4. PACKAGING SPECIFICATION: PK-180419-005
 5. UL:0LFB2 UL496 FILE NO. E345583
 6. ELV AND ROHS COMPLIANT
 7. FOR USE WITH: 13.5 MM X 13.5 MM COB LED
 8. WIRE GAUGE: 18, 20, AND 22 AWG, SOLID OR STRANDED WITH TIN OVERCOAT. STRIP LENGTH 10MM +2.0/-0.0MM.
 9. ALL DIMENSIONS IN PARENTHESES (XX.XX) ARE FOR REFERENCE ONLY

ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZABJANOVSKI 2017/02/21 CHKD: APPR: BP/ISZCZOR 2017/03/07 REV	DESCRIPTION	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE				
			4 PLACES	± ---	± ---	MCOLE	2013/12/09					
			3 PLACES	± ---	± ---	CHECKED BY	DATE					
			2 PLACES	± 0.13	± ---	MCOLE	2013/12/09	DOCUMENT NO. molex SD-180414-112				
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE					
			0 PLACE	± ---	± ---	DMCGOWAN	2013/12/09	SHEET NO. 1 OF 5				
			ANGULAR ±1/2°		MATERIAL NO.							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			C4				SIZE B					

P/N 180414-2112 HOLDER ASSEMBLY
(0.75 POCKET DEPTH)



ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZABJANOVSKI 2017/02/21 CHKD: APPR: BPI/SZCZOR 2017/03/07 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE			
		4 PLACES	± ---	± ---	MCOLE	2013/12/09				
		3 PLACES	± ---	± ---	CHECKED BY	DATE				
		2 PLACES	± 0.13	± ---	MCOLE	2013/12/09	DOCUMENT NO. SD-180414-112			
		1 PLACE	± 0.25	± ---	APPROVED BY	DATE				
		0 PLACE	± ---	± ---	DMCGOWAN	2013/12/09	SHEET NO. 2 OF 5			
		ANGULAR ±1/2°		MATERIAL NO.						
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				




RECOMMENDED MOUNTING DIMENSIONS

ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZABJANOVSKI 2017/02/21 CHKD: APPR: BPI SZCZOR 2017/03/07	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE		
			4 PLACES	± ---	± ---	MCOLE	2013/12/09			
			3 PLACES	± ---	± ---	CHECKED BY	DATE			
			2 PLACES	± 0.13	± ---	MCOLE	2013/12/09			
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE			
			0 PLACE	± ---	± ---	DMCGOWAN	2013/12/09	molex		
			ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.			SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-180414-112			3 OF 5
			C4	REV		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

10	9	8	7	6	5	4	3	2	1
COB MFG	TYPE	DIM 'X'	DIM 'Y'	DIM 'Z'	DIM 'D'	OFFSET			
VOSSLOH-SCHWABE	DMC122C	13.5	13.5	1.0	10.0	0.10			


ILLUSTRATION OF P/N 180414-1112 HOLDER MATED WITH LED



ENTER DESCRIPTION EC NO: SSL2017-0024 DRAWN: ZABJANOVSKI 2017/02/21 CHKD: APPR: BP/JSZCZOR 2017/03/07 C4	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY	DATE	TITLE COB LED HOLDER ASSEMBLY 13.5 MM X 13.5 MM SQUARE			
			4 PLACES	± ---	± ---	MCOLE	2013/12/09				
			3 PLACES	± ---	± ---	CHECKED BY	DATE				
			2 PLACES	± 0.13	± ---	MCOLE	2013/12/09				
			1 PLACE	± 0.25	± ---	APPROVED BY	DATE				
			0 PLACE	± ---	± ---	DMCGOWAN	2013/12/09	DOCUMENT NO. SD-180414-112		SHEET NO. 4 OF 5	
			ANGULAR ±1/2°		MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART						
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								


	10	9	8	7	6	5	4	3	2	1
	COB MFG	TYPE			DIM 'X'	DIM 'Y'	DIM 'Z'	DIM 'D'	OFFSET	
	CITIZEN	CLL020, CLL022, CLU024, CLU026, CLU028			13.5	13.5	0.90	11.2	0.15	
F	SEOUL	ZC6			13.5	13.5	0.90	10.0	0.15	
	TRIDONIC	SLE G5 LES10			13.5	13.5	0.90	9.4	0.15	
	CITIZEN	CLU025, CLU027			13.5	13.5	0.90	7.4	0.15	
	CITIZEN	CLU700, CLU701			13.5	13.5	0.90	7.8	0.15	
	EVERLIGHT	EAHP1313WA*, EAHP1313WB*, EAHP1313WC*			13.5	13.5	0.90	10.8	0.15	
	EVERLIGHT	EA1313 36V/3W			13.5	13.5	0.90	10.8	0.15	
E	EVERLIGHT	EA1313 36V/6W			13.5	13.5	0.90	10.8	0.15	
	EVERLIGHT	EA1313 36V/10W			13.5	13.5	0.90	10.8	0.15	
	EVERLIGHT	EA1313 36V/13W			13.5	13.5	0.90	10.8	0.15	
	VOSSLOH-SCHWABE	DMC122C			13.5	13.5	1.00	10.0	0.25	

ILLUSTRATION OF P/N 180414-2112 HOLDER MATED WITH LED



SECTION W-W

DETAIL 2
SCALE 4:1



ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: SSL2017-0024		F=0		mm		MM ONLY		2:1		METRIC		THIRD ANGLE PROJECTION	
DRAWN: ZABJANOVSKI 2017/02/21		F=0		INCH		DRAWN BY DATE		TITLE		COB LED HOLDER ASSEMBLY			
CHKD: BPTISZCZOR 2017/03/07		F=0		4 PLACES ± --- ± ---		MCOLE 2013/12/09		CHECKED BY DATE		13.5 MM X 13.5 MM SQUARE			
APPR: BPTISZCZOR 2017/03/07		F=0		3 PLACES ± --- ± ---		MCOLE 2013/12/09		APPROVED BY DATE					
		F=0		2 PLACES ± 0.13 ± ---		DMCGOWAN 2013/12/09		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				1 PLACE ± 0.25 ± ---		SEE CHART				SD-180414-112		5 OF 5	
				0 PLACE ± --- ± ---									
				ANGULAR ± 1/2°									
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									