


2007857-2 Product Details



Active

Impact High Density Backplane Connectors

IMP,H,5PR16C,LGOpenNo key,4.9,Sn0.39

2007857-2

TE Internal Number: 2007857-2

Product Highlights View All

- Connector Style = Header
- 160/Signal, 80/Ground
- 240 Positions
- Header Type = Partially Shrouded
- Board-to-Board Configuration = Right Angle, Vertical

Share Print Email

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through
Distributor

Feedback

Documents Features Compliance

Please Note:
Use the Product Drawing for all design activity

Product Type Features

PCB Mount Retention Type	Action/Compliant Tail and Screw(s)
PCB Mount Alignment Type	Locating Post(s)

Electrical Characteristics

Impedance (Ω)	100
Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	120
Operating Voltage (VDC)	120

Dimensions

Tail Length (mm [in])	1.2 [0.047]
Length (X-Axis) (mm [in])	36.90 [1.4528]
Width (Z-Axis) (mm [in])	24.80 [0.9763]
Profile Height (Y-Axis) (mm [in])	11.95 [0.470]
PCB Hole Diameter (mm [in])	0.39 [0.015]

Body Features

Header Type	Partially Shrouded
-------------	--------------------

Contact Features

Contact Type	Pin
Contact Length (mm [in])	4.90 [0.193]
Contact Plating, Termination Area, Material	Matte Tin
Contact Plating, Termination Area, Thickness (µm [µin])	1.27 [50]
Contact Base Material	Copper-Nickel-Silicon
Underplate Material	Nickel
Underplate Material Thickness (µm [µin])	1.27 [50.000]

Housing Features

Connector Style	Header
End Wall Location	Open
Housing Color	Black
Housing Material	LCP (Liquid Crystal Polymer)

Configuration Features

Connector Contact Configuration (No. of Pos./Type)	160/Signal, 80/Ground
Number of Positions	240
Number of Differential Pairs Per Column	5
Number of Columns	16
Number of Rows	15
Shrouded	Yes - Partial
Guide Location	Left
Tail Orientation	In-line

Industry Standards

RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0
CSA Certified	Yes

Environmental

Operating Temperature (°C [°F])	-55 - +85 [-67 - +185]
---------------------------------	------------------------

Conditions for Usage

Board-to-Board Configuration	Right Angle, Vertical
------------------------------	-----------------------

Operation/Application

Industry Application	Networking (Communications)
----------------------	-----------------------------

Packaging Features

Packaging Method	Tube/Box
------------------	----------

Other

Brand	TE Connectivity
-------	-----------------

Related Products

Not quite the product you're looking for?
Find Similar Products

View Part in Product Feature Selector

Check for Tooling

Corporate Information

About TE
Investors
News Room
Supplier Portal
Careers
Terms & Conditions
Privacy Policy
Global Accessibility Statement

Quick Links

Distributor Inventory
Product Cross Reference
Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat With Us
Find a Phone Number
Knowledge Base
Manage Your Account

Keep Me Informed

