



This item includes:

|                                                                                                                                                                                                       |                                                                                                                                                                                                       |                                                                                                                                                                                                       |                                                                                                                   |   |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------|---|
|                                                                                                                      |                                                                                                                      |                                                                                                                      |                                | 4 |
| <b>Item No.: 221-412</b><br>Splicing connector with levers; for all conductor types; max. 4 mm²; 2-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent | <b>Item No.: 221-413</b><br>Splicing connector with levers; for all conductor types; max. 4 mm²; 3-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent | <b>Item No.: 221-415</b><br>Splicing connector with levers; for all conductor types; max. 4 mm²; 5-conductor; transparent housing; Surrounding air temperature: max 85°C (T85); 4,00 mm²; transparent | <b>Item No.: 221-500</b><br>Mounting carrier; 221 Series - 4 mm²; for DIN-35 rail mounting/screw mounting; orange |   |

Notes

|                            |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| General safety information | <b>NOTICE: Observe installation and safety instructions!</b> <ul style="list-style-type: none"><li>• Only to be used by electricians!</li><li>• Do not work under voltage/load!</li><li>• Use only for proper use!</li><li>• Observe national regulations/standards/guidelines!</li><li>• Observe technical specifications for the products!</li><li>• Observe the number of permissible potentials!</li><li>• Do not use damaged/dirty components!</li><li>• Observe conductor types, cross-sections and strip lengths!</li><li>• Insert conductor until it hits the product's backstop!</li><li>• Use original accessories!</li></ul> <b>To be sold only with installation instructions!</b> |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Physical data

|        |                        |
|--------|------------------------|
| Width  | 259 mm / 10.197 inches |
| Height | 63 mm / 2.48 inches    |
| Depth  | 155 mm / 6.102 inches  |



| Material data        |  |                                                                          |
|----------------------|--|--------------------------------------------------------------------------|
| Note (material data) |  | <a href="#">Information on material specifications can be found here</a> |
| Fire load            |  | 14.701 MJ                                                                |
| Weight               |  | 856.2 g                                                                  |

| Commercial data       |  |               |
|-----------------------|--|---------------|
| PU (SPU)              |  | 1 pcs         |
| Packaging type        |  | Box           |
| Country of origin     |  | QU            |
| GTIN                  |  | 4055143616997 |
| Customs tariff number |  | 85369010000   |

| Product Classification |  |                      |
|------------------------|--|----------------------|
| UNSPSC                 |  | 39121409             |
| eCl@ss 10.0            |  | 27-14-11-04          |
| eCl@ss 9.0             |  | 27-14-11-04          |
| ETIM 9.0               |  | EC000446             |
| ETIM 8.0               |  | EC000446             |
| ECCN                   |  | NO US CLASSIFICATION |

| Environmental Product Compliance |  |                        |
|----------------------------------|--|------------------------|
| RoHS Compliance Status           |  | Compliant,No Exemption |

| Downloads                                |  |                                                                                     |
|------------------------------------------|--|-------------------------------------------------------------------------------------|
| Environmental Product Compliance         |  |                                                                                     |
| Compliance Search                        |  |                                                                                     |
| Environmental Product Compliance 887-952 |  |  |

| Documentation |            |                  |  |                                                                                     |
|---------------|------------|------------------|--|-------------------------------------------------------------------------------------|
| Bid Text      |            |                  |  |                                                                                     |
| 887-952       | 19.02.2019 | xml<br>2.76 KB   |  |  |
| 887-952       | 23.01.2019 | docx<br>14.93 KB |  |  |