



+ RELAYS, CONTACTORS & SWITCHES

TIME DELAY RELAYS



✓ Active

TE CONNECTIVITY (TE)
2122D4YD=RLY,MINI,OFF,2P,125VD

Agastat | 2100 Miniature Timing

2122D4YD
TE Internal Number: 1423154-1

Not EU RoHS Compliant
Not EU ELV Compliant

Type of Control Knob

Input Voltage (VDC) 125

Timing Range (Off-Time) (seconds) .375 – 3

Mode of Operation Off-Delay

Delay Time .375 – 3 seconds

DOCUMENTATION

Catalog Pages/Data Sheets

5-1773450-5_sec12_2100

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Product Category Electromechanical Relays

Relay Type Time Delay

Product Type Relay

Enclosure Type Octal Conn, Adjustable

Configuration Features

Multiple Timing Ranges Without

Electrical Characteristics

Input Voltage (VDC) 125
Timing Range (Off-Time) (seconds) .375 – 3
Actuating System DC

Contact Features

Type of Control Knob
Delay Time .375 – 3 seconds
Contact Arrangement 2 Form C, DPDT, 2 C/O

Termination Features

Termination Type 8-Pin Octal Style Plug

Mechanical Attachment

Mounting Type Chassis Mount

Dimensions

Dimensions (L x W x H) (Approximate) 63.5 x 38.6 x 123.9 mm [2.501 x 1.52 x 4.881 in]

Usage Conditions

Operating Temperature Range (°C) -55 – 85

Operation/Application

Mode of Operation Off-Delay

Other

Repeatability (Max) ±5% @ 25°C, ±7% @ 85°C, ±8% @ 55°C

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF